

## Fan Coil Valve

	COOLING CAPACITY TON*	TYPE	FCU VALVE	SIZE (INCH)	DN	Cv	CLOSE OFF PRESSURE PSI (kPa)	CONNECTION	POWER SUPPLY	LIST PRICE
	1	2-way, Electric-Return	RB215+FRU230-3	1/2	15	1.8	87 (600)	Female ISO7/1 end fitting	220VAC	5,600
	2-4			3/4	20	4.7	87 (600)	Female ISO7/1 end fitting	220VAC	5,600
	5			1	25	9.4	87 (600)	Female ISO7/1 end fitting	220VAC	5,800
	1	3-way, Electric-Return	RB315+FRU230-3	1/2	15	1.8	87 (600)	Female ISO7/1 end fitting	220VAC	5,800
	2-4			3/4	20	4.7	87 (600)	Female ISO7/1 end fitting	220VAC	5,800
	5			1	25	9.4	87 (600)	Female ISO7/1 end fitting	220VAC	6,000
	1	2-way, Spring-Return	Z215S-230	1/2	15	2.0	60 (414)	BSP end fitting	220VAC	4,500
	2			3/4	20	2.5	50 (344)	BSP end fitting	220VAC	4,500
	2-2.5			1	25	3.0	44 (303)	BSP end fitting	220VAC	4,700
	2-5			1	25	8.0	20 (137)	BSP end fitting	220VAC	4,700
	1	3-way, Spring-Return	Z315S-230	1/2	15	2.5	60 (414)	BSP end fitting	220VAC	5,100
	2-2.5			3/4	20	3.0	50 (344)	BSP end fitting	220VAC	5,200
	3			1	25	3.5	44 (303)	BSP end fitting	220VAC	5,600
	1	2-way, Spring-Return	690420900001 (VAL09035)	1/2	15	3.7	29 (200)	BSP end fitting	220VAC	3,500
	2-3			3/4	20	3.7	29 (200)	BSP end fitting	220VAC	3,700
	4-5			1	25	7.9	11.6 (80)	BSP end fitting	220VAC	4,000
	1	3-way, Spring-Return	VAL10380	1/2	15	3.7	21.7 (150)	BSP end fitting	220VAC	3,400
	2-3			3/4	20	5.3	14.5 (100)	BSP end fitting	220VAC	3,600
	4-5			1	25	6.6	14.5 (100)	BSP end fitting	220VAC	4,200

\* Calculated by standard flow rate @ 2.4 GPM/Ton, ΔP = 5 PSI

## Trane Fan Coil Valve - Spare Parts



P/N	DESCRIPTION	LIST PRICE
70-MOT00003	HYSTERESIS MOTOR 5 RPM, 220V, 50HZ (UNIVERSAL MOTORIZED VALVE)	1,200
690424220001	HYSTERESIS MOTOR 5 RPM, 220V, 50HZ FOR TRANE VAL09035, 9036, 9037, 9038, 9039, 10312	1,200