



Air-Cooled Condensing Units

Model RAUS

Cooling capacity 15.4 - 41.7 kW

Model RAUX

Cooling capacity 14.6 - 39.6 kW

Heating capacity 15.8 - 42.8 kW



Air-Cooled Condensing Units



**Condensing units with scroll compressors,
for outdoor installation**

Range description

- **RAUS** cooling only condensing units
- **RAUX** heat pump condensing units

Unit description

- Scroll compressor
- Fans propeller type
- High efficiency condenser coil with seamless copper tubes and aluminium fins
- Microprocessor-based controller to manage unit on/off mode, operating mode setting, parameters setting, and error code display
- Low ambient condensing pressure control with variable fan speed modulation
- Plastic condensing coil protection grille
- Electrical panel
- Casing and panels in galvanised and powder painted steel

Options

- Compressors sound jackets
- Soft - starter
- Control panel electric heater with thermostat
- Phase failure protection relay
- Epoxy coated condensing coils

Accessories

- Remote control panel
- Communication card RS485
- Connection kit including:
 - thermostatic expansion valve
 - filter dryer with sight glass
 - liquid line solenoid valve
- Liquid receiver
- Service valves on the suction, liquid and equalization lines
- Rubber anti vibration mounts

Advantages

- RAUS/RAUX condensing units are designed for optimum energy efficiency with reduced footprint.
- Low power consumption thanks to high efficiency condenser coils with integrated sub cooling circuit enhancing both capacity and efficiency.



Operating range		RAUS	RAUX cooling	RAUX heating
Operating outdoor air temperature range (min./max.)	(°C)	5/43	5/43	-5/20
Evaporating temperature range (min./max.)	(°C)	-12/12	-12/12	-
Condensing temperature range (min./max.)	(°C)	-	-	37/58
Power supply	(V/Ph/Hz)	400/3+n/50		

Cooling Only Version

General data

RAUS	Unit size	040	060	070	080	100	110
Cooling (1)							
Cooling capacity	kW	15.40	21.20	24.50	28.60	37.20	41.70
Total power input (including fans)	kW	4.80	7.20	8.70	9.80	12.10	14.10
EER (including fans)		3.17	2.96	2.83	2.93	3.07	2.95
Number of refrigerant circuits		1					
Number of compressors		1					
Compressor type		Scroll					
Sound pressure level (2)	dB(A)	50	46	47	48	48	55
Sound power level (3)	dB(A)	76	72	73	74	75	81

(1) Outdoor temperature 35°C - evaporating temperature 5°C

(2) According to ISO 3744 at 5 m distance from the unit

(3) According to ISO 9614 for Eurovent certified units, or ISO 3744 for non-certified units

Heat Pump Version

General data

RAUX	Unit size	040	060	070	080	100	110
Cooling (1)							
Cooling capacity	kW	14.60	20.10	23.30	27.20	35.40	39.60
Total power input (including fans)	kW	4.85	7.16	8.65	9.76	12.12	14.10
EER (including fans)		3.01	2.81	2.69	2.79	2.92	2.81
Heating (2)							
Heating capacity	kW	15.80	21.50	25.10	29.20	37.90	42.80
Total power input	kW	5.33	7.40	8.59	10	12.76	14.10
COP		2.95	2.91	2.92	2.92	2.97	3.04
Number of refrigerant circuits		1					
Number of compressors		1					
Compressor type		Scroll					
Sound pressure level (3)	dB(A)	50	46	47	48	48	55
Sound power level (4)	dB(A)	76	72	73	74	75	81

(1) Outdoor temperature 35°C - evaporating temperature 5°C

(2) Outdoor temperature 7°C 90% R.H. - condensing temperature 50°C

(3) According to ISO 3744 at 5 m distance from the unit

(4) According to ISO 9614 for Eurovent certified units, or ISO 3744 for non-certified units

Dimensions and weights

	Unit size	040	060	070	080	100	110
A	mm	1125	1465	1465	1671	1671	1671
B	mm	440	560	560	560	560	560
C	mm	1444	1448	1448	1687	1687	1687
Shipping weight RAUS	kg	151	221	230	259	262	272
Shipping weight RAUX	kg	169	243	252	293	296	306



Easy-to-use microprocessor-based controller.



Trane® is a brand of Ingersoll Rand®. Ingersoll Rand (NYSE:IR) advances the quality of life by creating comfortable, sustainable and efficient environments. Our people and our family of brands—including Ingersoll Rand®, Trane®, Thermo King® and Club Car® — work together to enhance the quality and comfort of air in homes and buildings; transport and protect food and perishables; and increase industrial productivity and efficiency. We are a global business committed to a world of sustainable progress and enduring results.



engineer.trane.com

trane.com

ingersollrand.com