



ILLUSION

concealed air handling units

12,000-60,000 BTU

MCD Series

Standard Indoor Units

Specifications: 200-240/1/50 or 220/-240/1/60

Model	Cooling Capacity	Airflow		Uncreated Dimensions						Weight	
				Height		Width		Depth			
	(BTU)	CFM	CMH	in	mm	in	mm	in	mm	lb.	kg.
Uncased											
MCD512D	12,000	300	510	10	254	37.4	950	18.9	480	44	20
MCD518D	18,000	450	764	10	254	37.4	950	18.9	480	44	20
MCD524D	24,000	600	1,019	10.0	254	37.4	950	20.5	520	53	24
MCD530D	30,000	750	1,274	10.0	254	43.3	1,100	20.5	520	57	26
MCD536D	36,000	900	1,529	10.0	254	49.2	1250	20.5	520	64	29
With Return Plenum & Filter Rack											
MCD048D	48,000	1,600	2,718	16.1	408	43.6	1,107	29.9	759	107	48.5
MCD060D	60,000	2,000	3,398	16.6	421	49.2	1,250	29.9	759	120	54.5