



STYLUS

Convertible Mini-Split 12,000-60,000 BTU MCX Series

Standard Indoor Units

Specifications: 200-240/1/50 or 220/-240/1/60

Model	Cooling Capacity (BTU)	Airflow		Cooling Nominal Capacity		Dimensions						Weight	
		CFM	CMH	kW	MBH	Height		Width		Depth		lb.	kg.
						in	mm	in	mm	in	mm		
MCX512E	12,000	300	510	3.5	12	24.7	627	42.7	1085	9.0	229	71	32
MCX518E	18,000	450	765	5.3	18	24.7	627	42.7	1085	9.0	229	73	33
MCX524E	24,000	600	1,020	7	24	24.7	627	52.6	1,335	9.0	229	88	40
MCX530E	30,000	750	1,275	9	30	24.7	627	62.4	1,585	9.0	229	115	52
MCX536E	36,000	900	1,530	11	36	24.7	627	62.4	1585	9.0	229	123	56
MCX542E	42,000	1,050	1,785	12	42	24.7	627	72.2	1,835	9.0	229	132	60
MCX548E	48,000	1,200	2,040	14	48	24.7	627	72.2	1,835	9.0	229	137	62
MCX560E	60,000	1500	2550	17.5	60	24.7	627	82.1	2085	9.0	229	172	78