



Trane AHU Starter Panel : Standard Model
For Trane Commercial AHU Motors (Model : TTH, TWE and TTV) and general AHU Motors

Standard Panel with Manual Thermostat

PANEL P/N	CDU MODEL	AHU MODEL	STARTER TYPE	POWER SUPPLY	MOTOR HP	MOTOR kW	MANUAL THERMOSTAT P/N	LIST PRICE
690401300001	TTK060	TTH060	DOL	380V/3PH/50Hz	0.75	0.55	Multi-Stage (P/N : 690411070001)	30,000
690420050001	TTA075	TTH075	DOL		1	0.75	Multi-Stage (P/N : 690411070001)	30,000
	TTA100	TTH100	DOL		2	1.5		30,000
	TTA120	TTH120/TWE120	DOL		2	1.5		30,000
	TTA150	TTH160/TWE160	DOL		2	1.5		30,000
690401310001	TTA180	TTH180/TWE180	DOL		3	2.2	Multi-Stage (P/N : 690411070001)	30,000
	TTA200	TTH210/TWE210	DOL		3	2.2		30,000
	TTA240	TTH240/TWE240	DOL		5	3.7		30,000
	RAUP250	TTV250	DOL		5	3.7		30,000
690406080001	RAUP300	TTV300	Y-D		7.5	5.5	Multi-Stage (P/N : 690411070001)	41,000
	RAUP400	TTV400	Y-D		7.5	5.5		41,000
	RAUP500	TTV500	Y-D		10	7.5		41,000
	RAUP600	TTV600	Y-D	15	11	41,000		



Size of Panel : 350x500x200mm. (WxHxD) for DOL, 450x600x200mm. (WxHxD) for Y-D

Trane AHU Starter Panel : Standard Model For Trane Commercial AHU Motors (Model : TTH, TWE and TTV) and general AHU Motors

Standard Panel with Digital Thermostat

PANEL P/N	CDU MODEL	AHU MODEL	STARTER TYPE	POWER SUPPLY	MOTOR HP	MOTOR KW	MANUAL THERMOSTAT P/N	LIST PRICE
690406070001	TTK060	TTH060	DOL	380V/3PH/50Hz	0.75	0.55	Digital Multi-Stage (P/N : 024-0495-060)	31,500
	TTA075	TTH075	DOL		1	0.75	Digital Multi-Stage (P/N : 024-0495-060)	31,500
	TTA100	TTH100	DOL		2	1.5		31,500
	TTA120	TTH120/TWE120	DOL		2	1.5		31,500
690406100001	TTA150	TTH160/TWE160	DOL		2	1.5	Digital Multi-Stage (P/N : 024-0495-060)	31,500
	TTA180	TTH180/TWE180	DOL		3	2.2		31,500
	TTA200	TTH210/TWE210	DOL		3	2.2		31,500
	TTA240	TTH240/TWE240	DOL		5	3.7	Digital Multi-Stage (P/N : 024-0495-060)	31,500
690406110001	RAUP250	TTV250	DOL		5	3.7	Digital Multi-Stage (P/N : 024-0495-060)	31,500
	RAUP300	TTV300	Y-D		7.5	5.5		43,000
	RAUP400	TTV400	Y-D		7.5	5.5		43,000
	RAUP500	TTV500	Y-D		10	7.5	Digital Multi-Stage (P/N : 024-0495-060)	43,000
	RAUP600	TTV600	Y-D	15	11		43,000	



Size of Panel : 350x500x200mm. (WxHxD) for DOL, 450x600x200mm. (WxHxD) for Y-D



Trane AHU Starter Panel for Water Coil AHU
For Trane Commercial Water Coil AHU motor (Model : BDHA, BDCB, BDVA)



PANEL P/N	AHU MODEL	CAPACITY		STARTER TYPE	MOTOR		RLA/LRA (Amp)	POWER SUPPLY	DESCRIPTION	DIGITAL THERMOSTAT P/N	LIST PRICE
		TONS	MBH		HP	kW					
N/A	BDHA20	5	60	DOL	0.75	0.55	1.61/8.4	380V/3PH/50HZ	TRANE STARTER PANEL DOL TYPE WITH DISPLAY PROPORTIONAL THERMOSTAT 0-10VDC POWER SUPPLY 24VAC**	70-TERM00012	33,000
690424310001	BDHA25	6.25	75	DOL	1	0.75	1.99/11.0				33,000
70-ELEEC0165	BDHA34	8.33	100	DOL	2	1.5	3.66/21.0				33,000
70-ELEEC0166	BDHA40	10	120	DOL	2	1.5	3.66/21.0				33,000
70-ELEEC0167	BDHA50/BDCB50	13.33	160	DOL	2	1.5	3.66/21.0				33,000
690418560001	BDHA60/BDCB60	15	180	DOL	3	2.2	5.08/34.0				33,000
N/A	BDHA70/BDCB70	17.5	210	DOL	3	2.2	5.08/34.0				33,000
N/A	BDHA80/BDCB80	20	240	DOL	5	3.7	8.03/63.0				33,000
N/A	BDVA075	19.83	238	DOL	5	3.7	8.03/63.0				33,000
N/A	BDVA090	23.33	280	Y-D	7.5	5.5	12.0/79.0				44,500
N/A	BDVA120	31.66	380	Y-D	7.5	5.5	12.0/79.0				44,500
N/A	BDVA150	47.5	570	Y-D	10	7.5	15.2/110.0				45,500
N/A	BDVA180	55	660	Y-D	15	11	22.0/153.0				47,500