

Flow Switch

2



BRAND	P/N	MODEL	DESCRIPTION	SIZE	LIST PRICE
McDonnell	026-5211	FS4-3	Flow switch 150 psi, for pipe 1-6" indoor type	Dia 1" NPT	8,700
McDonnell	026-5213	FS8-W	Flow switch 150 psi, for pipe 1-6" outdoor type	Dia 1" NPT	11,500
McDonnell	N/A	FS7-4	Flow switch 150 psi, for pipe 1-1/4" to 16" indoor type	Dia 1-1/4" NPT	CALL
McDonnell	N/A	FS7-4W	Flow switch 150 psi, for pipe 1-1/4" to 16" outdoor type NEMA 4X	Dia 1-1/4" NPT	CALL
Dwyer	N/A	V8	Flotect Vane Operated Flow Switch (Indoor type) Service: Compatible gases or liquids. Temperature Limit: 100°C Pressure Limit: 150 psig (10 bar) Pipe size: 1-6"	Dia 1" Male NPT	CALL
Dwyer	N/A	V8-WP2	Flotect Vane Operated Flow Switch (Outdoor type) Service: Compatible gases or liquids. Temperature Limit: 100°C Pressure Limit: 150 psig (10 bar) Switch Type: SPDT snap switch Pipe size: 1-6"	Dia 1" Male NPT	CALL

Trane Rubber Isolator

FOR TTK



DESCRIPTION	SIZE	LIST PRICE
Rubber Isolator Kit for TTK512-524 (4 pieces/set)	TT7745E-SP	200
Rubber Isolator Kit for TTK524LB5-060 (4 pieces/set)	TT7745C-SP	200