TRANE®

# Cased Aluminum Dedicated Upflow / Downflow Coils Convertible to Horizontal with Kit

# 4PXC

**Heat Pump /Cooling Coils for R-410A**
**2 - 5 Ton**



**PUB. NO. 22-1902-2A**

TRANE®

# Aluminum Heat Pump Coil Nomenclature

## Heat Pump/ Cooling Coils




**Refrigerant Type**
4 = R-410A

**Series**
T = Premium (Heat Pump)
N = Premium (Cooling and HP)
P = Premium High Efficiency - Dedicated position (Cooling and HP)
C = Standard (Cooling Only)
F = Entry Level (Cooling Only)

**Coil Design**
X = Direct Expansion Evaporator Coil

**Coil Feature**
C = Cased A Coil
A = Uncased A Coil
F = Cased Horizontal Flat Coil

**Coil Width (Cased/Uncased)**
A = 14.5" /13.3"
B = 17.5" / 16.3"
C = 21.0" / 19.8"
D = 24.5" / 23.3"
H = 10.5"

**Refrigerant Line Coupling / Airflow Configuration**
0 = Brazed
U = Upflow only, convertible to Horizontal Left
D = Downflow only, convertible to Horizontal Right

**Nominal Capacity in 1000's (BTUH) / Model Number Distinguisher**

**Major Design Change**

**Efficiency**
C = Standard
S = High Efficiency (derived from 10 SEER products)
Z = High Efficiency (TXV modulates to 50%)

**Refrigerant Control**
3 = TXV - Non-Bleed

**Coil Circuitry**
H = Heat Pump
C = Cooling

**Airflow Configuration**
A = Upflow
U = Upflow /Downflow
D = Downflow
R = Downflow / Horizontal Right
H = Horizontal Left/Right
C = Convertible - Upflow, Downflow, Left or Right

**Minor Design Change**

**Service Digit - Not Orderable**

© 2017 Trane All rights reserved

Pub. No. 22-1902-2A

# General Data

## PRODUCT SPECIFICATIONS[1] -- 4 PXC - SPLIT SYSTEM HEAT PUMP / COOLING CASED DEDICATED UPFLOW COMFORT™ COILS [2]

| Model | 4PXCAU24BS3HAA | 4PXCBU24BS3HAA | 4PXCBU30BS3HAA | 4PXCCU30BS3HAA |
|---|---|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 2 / 20 | 2 / 20 | 3 / 14 | 3 / 14 |
| Face Area (sq.ft.) | 3.0 | 3.0 | 3.5 | 3.5 |
| Tube Size | 3/8 | 3/8 | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing | See outline drawing | See outline drawing |
| **REFRIGERANT CONNECTIONS** | R-410A BRAZED | R-410A BRAZED | R-410A BRAZED | R-410A BRAZED |
| Line Size -- Gas (in.) | 3/4 | 3/4 | 3/4 | 3/4 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 21.35 x 17.5 x 26.5 | 21.35 x 20.5 x 26.5 | 21.35 x 20.5 x 26.5 | 21.35 x 24 x 26.5 |
| Uncrated | 17.6 x 14.5 x 21.5 | 17.6 x 17.5 x 21.5 | 17.6 x 17.5 x 21.5 | 17.6 x 21 x 21.5 |
| **WEIGHT (lbs)** | | | | |
| Shipping -- Net | 39 / 31 | 42 / 34 | 47 / 39 | 49 / 41 |

| Model | 4PXCBU36BS3HAA | 4PXCCU36BS3HAA | 4PXCBU42BS3HAA | 4PXCCU42BS3HAA |
|---|---|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 3 / 12 | 3 / 12 | 3 / 14 | 3 / 14 |
| Face Area (sq.ft.) | 5.0 | 5.0 | 5.5 | 5.5 |
| Tube Size | 3/8 | 3/8 | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing | See outline drawing | See outline drawing |
| **REFRIGERANT CONNECTIONS** | R-410A BRAZED | R-410A BRAZED | R-410A BRAZED | R-410A BRAZED |
| Line Size -- Gas (in.) | 7/8 | 7/8 | 7/8 | 7/8 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 26.35 x 20.5 x 26.5 | 26.35 x 24 x 26.5 | 30.65 x 20.5 x 26.5 | 30.65 x 24 x 26.5 |
| Uncrated | 22.6 x 17.5 x 21.5 | 22.6 x 21 x 21.5 | 26.9 x 17.5 x 21.5 | 26.9 x 21 x 21.5 |
| **WEIGHT (lbs)** | | | | |
| Shipping -- Net | 54 / 46 | 56 / 48 | 61 / 53 | 64 / 56 |

[1] These indoor coils are A.H.R.I. certified with various split system air conditioners and heat pumps (A.H.R.I. Standard 210/240). Refer to the Split System Outdoor product information site or www.ahrinet.org

[2] Convertible to Horizontal Left with Kit

# General Data

## PRODUCT SPECIFICATIONS[1] -- 4 PXC - SPLIT SYSTEM HEAT PUMP / COOLING CASED DEDICATED UPFLOW COMFORT™ COILS [2]

| Model | 4PXCBU48BS3HAA | 4PXCCU48BS3HAA | 4PXCDU48BS3HAA |
|---|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 3 / 14 | 3 / 14 | 3 / 14 |
| Face Area (sq.ft.) | 6.0 | 6.0 | 6.0 |
| Tube Size | 3/8 | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing | See outline drawing |
| **REFRIGERANT CONNECTIONS** | R-410A BRAZED | R-410A BRAZED | R-410A BRAZED |
| Line Size -- Gas (in.) | 7/8 | 7/8 | 7/8 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 30.65 x 20.5 x 26.5 | 30.65 x 24 x 26.5 | 30.65 x 27.5 x 26.5 |
| Uncrated | 26.9 x 17.5 x 21.5 | 26.9 x 21 x 21.5 | 26.9 x 24.5 x 21.5 |
| **WEIGHT (lbs)** | | | |
| Shipping -- Net | 61 / 53 | 64 / 56 | 68 / 60 |

| Model | 4PXCCU60BS3HAA | 4PXCDU60BS3HAA |
|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 3 / 12 | 3 / 12 |
| Face Area (sq.ft.) | 6.0 | 6.0 |
| Tube Size | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing |
| **REFRIGERANT CONNECTIONS** | R-410A BRAZED | R-410A BRAZED |
| Line Size -- Gas (in.) | 3/4 | 7/8 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 34.45 x 24 x 26.5 | 34.45 x 27.5 x 26.5 |
| Uncrated | 30.7 x 21 x 21.5 | 30.7 x 24.5 x 21.5 |
| **WEIGHT (lbs)** | | |
| Shipping -- Net | 73 / 65 | 77 / 69 |

[1] These indoor coils are A.H.R.I. certified with various split system air conditioners and heat pumps (A.H.R.I. Standard 210/240). Refer to the Split System Outdoor product information site or www.ahrinet.org

[2] Convertible to Horizontal Left with Kit

# General Data

## PRODUCT SPECIFICATIONS[1] -- 4 PXC - SPLIT SYSTEM HEAT PUMP / COOLING CASED DEDICATED DOWNFLOW COMFORT™ COILS [2]

| Model | 4PXCAD24BS3HDA | 4PXCBD24BS3HDA | 4PXCBD30BS3HDA | 4PXCCD30BS3HDA |
|---|---|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 2 / 20 | 2 / 20 | 3 / 14 | 3 / 14 |
| Face Area (sq.ft.) | 3.0 | 3.0 | 3.5 | 3.5 |
| Tube Size | 3/8 | 3/8 | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing | See outline drawing | See outline drawing |
| **REFRIGERANT** | R-410A | R-410A | R-410A | R-410A |
| **CONNECTIONS** | BRAZED | BRAZED | BRAZED | BRAZED |
| Line Size -- Gas (in.) | 3/4 | 3/4 | 3/4 | 3/4 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 21.35 x 17.5 x 26.5 | 21.35 x 20.5 x 26.5 | 21.35 x 20.5 x 26.5 | 21.35 x 24 x 26.5 |
| Uncrated | 17.6 x 14.5 x 21.5 | 17.6 x 17.5 x 21.5 | 17.6 x 17.5 x 21.5 | 17.6 x 21 x 21.5 |
| **WEIGHT (lbs)** | | | | |
| Shipping -- Net | 39 / 31 | 42 / 34 | 47 / 39 | 49 / 41 |

| Model | 4PXCBD36BS3HDA | 4PXCCD36BS3HDA | 4PXCBD42BS3HDA | 4PXCCD42BS3HDA |
|---|---|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 3 / 12 | 3 / 12 | 3 / 14 | 3 / 14 |
| Face Area (sq.ft.) | 5.0 | 5.0 | 5.5 | 5.5 |
| Tube Size | 3/8 | 3/8 | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing | See outline drawing | See outline drawing |
| **REFRIGERANT** | R-410A | R-410A | R-410A | R-410A |
| **CONNECTIONS** | BRAZED | BRAZED | BRAZED | BRAZED |
| Line Size -- Gas (in.) | 7/8 | 7/8 | 7/8 | 7/8 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 26.35 x 20.5 x 26.5 | 26.35 x 24 x 26.5 | 30.65 x 20.5 x 26.5 | 30.65 x 24 x 26.5 |
| Uncrated | 22.6 x 17.5 x 21.5 | 22.6 x 21 x 21.5 | 26.9 x 17.5 x 21.5 | 26.9 x 21 x 21.5 |
| **WEIGHT (lbs)** | | | | |
| Shipping -- Net | 54 / 46 | 56 / 48 | 61 / 53 | 64 / 56 |

[1] These indoor coils are A.H.R.I. certified with various split system air conditioners and heat pumps (A.H.R.I. Standard 210/240). Refer to the Split System Outdoor product information site or www.ahrinet.org

[2] Convertible to Horizontal Right with Kit

# General Data

## PRODUCT SPECIFICATIONS[1] -- 4 PXC - SPLIT SYSTEM HEAT PUMP / COOLING CASED DEDICATED DOWNFLOW COMFORT™ COILS [2]

| Model | 4PXCBD48BS3HDA | 4PXCCD48BS3HDA | 4PXCDD48BS3HDA |
|---|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 3 / 14 | 3 / 14 | 3 / 14 |
| Face Area (sq.ft.) | 6.0 | 6.0 | 6.0 |
| Tube Size | 3/8 | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing | See outline drawing |
| **REFRIGERANT CONNECTIONS** | R-410A BRAZED | R-410A BRAZED | R-410A BRAZED |
| Line Size -- Gas (in.) | 7/8 | 7/8 | 7/8 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 30.65 x 20.5 x 26.5 | 30.65 x 24 x 26.5 | 30.65 x 27.5 x 26.5 |
| Uncrated | 26.9 x 17.5 x 21.5 | 26.9 x 21 x 21.5 | 26.9 x 24.5 x 21.5 |
| **WEIGHT (lbs)** | | | |
| Shipping -- Net | 61 / 53 | 64 / 56 | 68 / 60 |

| Model | 4PXCCD60BS3HDA | 4PXCDD60BS3HDA |
|---|---|---|
| **INDOOR COIL -- Type** | PLATE FIN | PLATE FIN |
| Rows / F.P.I. | 3 / 12 | 3 / 12 |
| Face Area (sq.ft.) | 6.0 | 6.0 |
| Tube Size | 3/8 | 3/8 |
| Refrigerant Control | Non-Bleed TXV | Non-Bleed TXV |
| Internal check valve | Yes | Yes |
| Drain Conn. Size (in.) | 3/4 NPT | 3/4 NPT |
| Duct Connections | See outline drawing | See outline drawing |
| **REFRIGERANT CONNECTIONS** | R-410A BRAZED | R-410A BRAZED |
| Line Size -- Gas (in.) | 3/4 | 7/8 |
| Line Size -- Liquid (in.) | 3/8 | 3/8 |
| **DIMENSIONS (in.)** | **H X W X D** | **H X W X D** |
| Crated (H x W x D) | 34.45 x 24 x 26.5 | 34.45 x 27.5 x 26.5 |
| Uncrated | 30.7 x 21 x 21.5 | 30.7 x 24.5 x 21.5 |
| **WEIGHT (lbs)** | | |
| Shipping -- Net | 73 / 65 | 77 / 69 |

[1] These indoor coils are A.H.R.I. certified with various split system air conditioners and heat pumps (A.H.R.I. Standard 210/240). Refer to the Split System Outdoor product information site or www.ahrinet.org

[2] Convertible to Horizontal Right with Kit



Pub. No. 22-1902-2A

# Performance Data

| PRESSURE DROP CHARACTERISTICS FOR COOLING AND HEAT PUMP COILS<br>AIRFLOW (SCFM) VS. PRESSURE DROP ACROSS WET COIL | | | | | | | |
|---|---|---|---|---|---|---|---|
| | PRESSURE DROP (INCHES OF WATER COLUMN) | | | | | | |
| MODEL | 0.1 | 0.15 | 0.2 | 0.25 | 0.3 | 0.35 | 0.4 |
| 4PXCAD24BS3HDA | 315 | 405 | 480 | 545 | 610 | 670 | 725 |
| 4PXCAU24BS3HAA | 340 | 430 | 510 | 585 | 650 | 715 | 775 |
| 4PXCBD24BS3HDA | 405 | 520 | 615 | 705 | 785 | 860 | 935 |
| 4PXCBD30BS3HDA | 510 | 645 | 760 | 865 | 965 | 1055 | 1140 |
| 4PXCBD36BS3HDA | 645 | 810 | 950 | 1080 | 1200 | 1305 | 1410 |
| 4PXCBD42BS3HDA | 585 | 745 | 880 | 1000 | 1115 | 1220 | 1315 |
| 4PXCBD48BS3HDA | 605 | 765 | 905 | 1035 | 1150 | 1255 | 1360 |
| 4PXCBU24BS3HAA | 435 | 555 | 660 | 755 | 840 | 920 | 995 |
| 4PXCBU30BS3HAA | 525 | 665 | 790 | 900 | 1000 | 1095 | 1180 |
| 4PXCBU36BS3HAA | 655 | 825 | 970 | 1100 | 1220 | 1330 | 1435 |
| 4PXCBU42BS3HAA | 625 | 790 | 935 | 1065 | 1185 | 1295 | 1400 |
| 4PXCBU48BS3HAA | 640 | 815 | 965 | 1095 | 1220 | 1335 | 1445 |
| 4PXCCD30BS3HDA | 520 | 660 | 780 | 885 | 985 | 1080 | 1165 |
| 4PXCCD36BS3HDA | 760 | 955 | 1125 | 1275 | 1415 | 1540 | 1665 |
| 4PXCCD42BS3HDA | 695 | 880 | 1040 | 1185 | 1315 | 1440 | 1555 |
| 4PXCCD48BS3HDA | 715 | 910 | 1075 | 1225 | 1360 | 1490 | 1610 |
| 4PXCCD60BS3HDA | 720 | 920 | 1095 | 1250 | 1390 | 1525 | 1655 |
| 4PXCCU30BS3HAA | 540 | 680 | 805 | 920 | 1020 | 1120 | 1210 |
| 4PXCCU36BS3HAA | 770 | 970 | 1145 | 1300 | 1440 | 1570 | 1696 |
| 4PXCCU42BS3HAA | 735 | 930 | 1105 | 1255 | 1400 | 1530 | 1655 |
| 4PXCCU48BS3HAA | 760 | 965 | 1140 | 1300 | 1445 | 1580 | 1710 |
| 4PXCCU60BS3HAA | 740 | 940 | 1120 | 1280 | 1425 | 1565 | 1695 |
| 4PXCDD48BS3HDA | 820 | 1035 | 1225 | 1395 | 1555 | 1700 | 1840 |
| 4PXCDD60BS3HDA | 815 | 1040 | 1235 | 1410 | 1575 | 1725 | 1870 |
| 4PXCDU48BS3HAA | 870 | 1100 | 1300 | 1485 | 1650 | 1805 | 1950 |
| 4PXCDU60BS3HAA | 835 | 1065 | 1265 | 1445 | 1615 | 1770 | 1915 |

Outline Drawing for Upflow models: 4PXCAU24BS3HAA, 4PXCBU24BS3HAA, 4PXCBU36BS3HAA, 4PXCCU36BS3HAA, 4PXCBU42BS3HAA, 4PXCCU42BS3HAA, 4PXCBU48BS3HAA, 4PXCCU48BS3HAA, 4PXCCU60BS3HAA, and Downflow models: 4PXCAD18BS3HDA, 4PXCBD18BS3HDA, 4PXCAD24BS3HDA, 4PXCBD24BS3HDA, 4PXCBD36BS3HDA, 4PXCCD36BS3HDA, 4PXCBD42BS3HDA, 4PXCCD42BS3HDA, 4PXCBD48BS3HDA, 4PXCCD48BS3HDA, 4PXCCD60BS3HDA




| MODEL | 4PXCAU24BS3<br>4PXCAD24BS3 | 4PXCBU24BS3<br>4PXCBD24BS3 | 4PXCBU36BS3<br>4PXCBD36BS3 | 4PXCCU36BS3<br>4PXCCD36BS3 | 4PXCBU42BS3<br>4PXCBD42BS3<br>4PXCBU48BS3<br>4PXCBD48BS3 | 4PXCCU42BS3<br>4PXCCD42BS3<br>4PXCCU48BS3<br>4PXCCD48BS3 | 4PXCCU60BS3<br>4PXCCD60BS3 |
|---|---|---|---|---|---|---|---|
| WEIGHT (LBS.) | 39 | 42 | 54 | 56 | 61 | 64 | 73 |
| REFRIGERANT CONTROL | TXV (NON-BLEED) | | | | | | |
| HEIGHT "A" (IN.) | 17-1/2 | 17-1/2 | 22-1/2 | 22-1/2 | 26-7/8 | 26-7/8 | 30-3/4 |
| OVERALL WIDTH "B" (IN.) | 14-1/2 | 17-1/2 | 17-1/2 | 21 | 17-1/2 | 21 | 21 |
| OPENING WIDTH "C" (IN.) | 13-5/8 | 16-5/8 | 16-5/8 | 20-1/8 | 16-5/8 | 20-1/8 | 20-1/8 |
| TOP OPENING "D" | 12-3/4 | 15-3/4 | 15-3/4 | 19-1/4 | 15-3/4 | 19-1/4 | 19-1/4 |
| GAS CONNECTION | 3/4 | 3/4 | 7/8 | 7/8 | 7/8 | 7/8 | 7/8 |
| LIQUID CONNECTION | 3/8 | 3/8 | 3/8 | 3/8 | 3/8 | 3/8 | 3/8 |
| MATCHED FURNACE WIDTH (NO ADAPTER REQUIRED) | 14-1/2 | 17-1/2 | 17-1/2 | 21 | 17-1/2 | 21 | 21 |
| DRAIN PAN | PLASTIC | | | | | | |

From Dwg. D345397 RevD

Pub. No. 22-1902-2A

Pub. No. 22-1902-2A

# Outline Drawing for Upflow models: 4PXCBU30BS3HAA, 4PXCCU30BS3HAA, and Downflow models: 4PXCBD30BS3HDA, 4PXCCD30BS3HDA







| MODEL | 4PXCBU30BS3<br>4PXCBD30BS3 | 4PXCCU30BS3<br>4PXCCD30BS3 |
|---|---|---|
| WEIGHT (LBS.) | 47 | 49 |
| REFRIGERANT CONTROL | TXV (NON-BLEED) | |
| HEIGHT (IN.) | 17-1/2 | 17-1/2 |
| OVERALL WIDTH (IN.) | 17-1/2 | 21 |
| OPENING WIDTH (IN.) | 16-5/8 | 20-1/8 |
| TOP OPENING | 15-3/4 | 19-1/4 |
| GAS CONNECTION | 3/4 | 3/4 |
| LIQUID CONNECTION | 3/8 | 3/8 |
| MATCHED FURNACE WIDTH (NO ADAPTER REQUIRED) | 17-1/2 | 21 |
| DRAIN PAN | PLASTIC | |

From Dwg. D345398 RevC

# Outline Drawing for Upflow models: 4PXCDU48BS3HAA, 4PXCDU60BS3HAA, and Downflow models: 4PXCDD48BS3HDA, 4PXCDD60BS3HDA




| MODEL | 4PXCDU48BS3<br>4PXCDD48BS3 | 4PXCDU60BS3<br>4PXCDD60BS3 |
|---|---|---|
| WEIGHT (LBS.) | 68 | 77 |
| REFRIGERANT CONTROL | TXV (NON-BLEED) | |
| HEIGHT (IN.) | 26-7/8 | 30-3/4 |
| OVERALL WIDTH (IN.) | 24-1/2 | 24-1/2 |
| OPENING WIDTH (IN.) | 23-5/8 | 23-5/8 |
| TOP OPENING | 22-3/4 | 22-3/4 |
| GAS CONNECTION | 7/8 | 7/8 |
| LIQUID CONNECTION | 3/8 | 3/8 |
| MATCHED FURNACE WIDTH (NO ADAPTER REQUIRED) | 24-1/2 | 24-1/2 |
| DRAIN PAN | PLASTIC | |

From Dwg. D345408 RevD

Pub. No. 22-1902-2A

# General Data

## HORIZONTAL CONVERSION KIT LISTED BY COIL MATCH

| Model Number | | Horizontal Kit No. |
|---|---|---|
| 4PXCAU24BS3HAA | 4PXCAD24BS3HDA | BAYCONV18A |
| 4PXCBU24BS3HAA | 4PXCBD24BS3HDA | |
| 4PXCBU30BS3HAA | 4PXCBD30BS3HDA | |
| 4PXCCU30BS3HAA | 4PXCCD30BS3HDA | |
| 4PXCBU36BS3HAA | 4PXCBD36BS3HDA | BAYCONV23A |
| 4PXCCU36BS3HAA | 4PXCCD36BS3HDA | |
| 4PXCBU42BS3HAA | 4PXCBD42BS3HDA | BAYCONV27A |
| 4PXCCU42BS3HAA | 4PXCCD42BS3HDA | |
| 4PXCBU48BS3HAA | 4PXCBD48BS3HDA | |
| 4PXCCU48BS3HAA | 4PXCCD48BS3HDA | |
| 4PXCDU48BS3HAA | 4PXCDD48BS3HDA | |
| 4PXCCU60BS3HAA | 4PXCCD60BS3HDA | BAYCONV30A |
| 4PXCDU60BS3HAA | 4PXCDD60BS3HDA | |

***Trane***
***6200 Troup Highway***
***Tyler, TX  75707***
***www.trane.com***

*For more information contact your local dealer (distributor)*

| | |
|---|---|
| Literature Order Number | 22-1902-2A |
| File Number | 22-1902-2A |
| Supersedes | 22-1902-2 |
| Date | 07/17 |

*Since **Trane** has a policy of continuous product improvement, **it** reserves the right to change design and specifications without notice.*