



Mini/Standard Koolman(R410A) Air-cooled (Heat Pump) Chiller

Cooling capacity:10.5~55.0kW

Comfortable & Environment-friendly-Smart Choice for Residential or Light Commercial Applications

Equipped with stable & high-efficiency hermetic compressor and plate heater exchanger, suitable fan coil units and air handing system to create more comfortable indoor environment.

New refrigerant R410A having no damage to ozone sphere makes the system more environment-friendly.



Koolman



Mini Koolman

Low noise & Comfortable

High-efficiency & low noise compressor with low speed fan lowers operating noise; With water as heat transfer medium, in summer, bringing more comfortable feeling by milder cold air and preventing condensation caused by low supply air temperature in refrigerant system.

Better Heating

Refrigerant-water heat transfer makes indoor pipes with hot water almost not affected by defrosting in winter, thus preventing uncomfortable feeling by indoor cold air.

Attractive Appearance

Specially designed by British designer, classic style perfectly harmonizes with surroundings, highlighting the excellent taste; 2 kinds of outdoor units available for meeting different installation place in residential or commercial applications.

Advanced Control

LCD microcomputer controller with various control modes, operation parameters and optional remote control; Modular or network control by optional central controller.

