









Fan Coil Valve

COOLING CAPACITY TON*	TYPE	FCU VALVE	SIZE (INCH)	DN	Cv	CLOSE OFF PRESSURE PSI (kPa)	CONNECTION	POWER SUPPLY	LIST PRICE
	2-way, Electric-Return	RB215+FRU230-3	1/2	15	1.8	87 (600)	Female ISO7/1 end fitting	220VAC	4,500
			3/4	20	4.7	87 (600)	Female ISO7/1 end fitting	220VAC	4,500
			1	25	9.4	87 (600)	Female ISO7/1 end fitting	220VAC	4,800
	3-way, Electric-Return	RB315+FRU230-3	1/2	15	1.8	87 (600)	Female ISO7/1 end fitting	220VAC	4,800
			3/4	20	4.7	87 (600)	Female ISO7/1 end fitting	220VAC	4,800
			1	25	9.4	87 (600)	Female ISO7/1 end fitting	220VAC	5,000
	2-way, Spring-Return	Z215S-230	1/2	15	2.0	60 (414)	BSP end fitting	220VAC	3,700
			3/4	20	2.5	50 (344)	BSP end fitting	220VAC	3,700
			1	25	3.0	44 (303)	BSP end fitting	220VAC	3,900
			2-5	25	8.0	20 (137)	BSP end fitting	220VAC	3,900
	3-way, Spring-Return	Z315S-230	1/2	15	2.5	60 (414)	BSP end fitting	220VAC	4,200
			3/4	20	3.0	50 (344)	BSP end fitting	220VAC	4,300
			3	25	3.5	44 (303)	BSP end fitting	220VAC	4,600
	2-way, Spring-Return	VAL09035	1/2	15	3.7	29 (200)	BSP end fitting	220VAC	2,500
			3/4	20	3.7	29 (200)	BSP end fitting	220VAC	2,600
			4-5	25	7.9	11.6 (80)	BSP end fitting	220VAC	2,800
	3-way, Spring-Return	VAL09038 / VAL101380	1/2	15	3.7	21.7 (150)	BSP end fitting	220VAC	2,600
			2-3	20	5.3	14.5 (100)	BSP end fitting	220VAC	2,700
			4-5	25	6.6	14.5 (100)	BSP end fitting	220VAC	3,200

* Calculated by standard flow rate @ 2.4 GPM/Ton, ΔP = 5 PSI

Trane Fan Coil Valve - Spare Parts



P/N	DESCRIPTION	LIST PRICE
70-MOT00003	HYSTERESIS MOTOR 5 RPM, 220V, 50HZ FOR VAL09035, VAL09037, VAL00069C, VAL00034C, VAL00071C	900