



Trane Rubber Isolator



FOR TTA/RAUP

DESCRIPTION	SIZE	LIST PRICE
Trane Rubber Isolator for TTA/RAUP (4 pieces/set) 4 pieces for TTA075-TTA240 6 pices for RAUP250-RAUP300 8 pices for RAUP400-RAUP600	028-0954-4	1,000

FOR TTK



DESCRIPTION	SIZE	LIST PRICE
Rubber Isolator Kit for TTK512-524 (4 pieces/set)	TT7745E-SP	100
Rubber Isolator Kit for TTK524LB5-060 (4 pieces/set)	TT7745C-SP	100

2

Spring Isolator



OSM (แบบตั้ง)



USH (แบบแขวน)

SPRING แบบตั้ง (OSM)

MODEL	P/N	RATE CAP		MOUNT		SPRING			LIST PRICE
		KGS	LBS	KG / MM	LBS / INCH	COLOR CODE	OD	HT	
OSM-A -10	N/A	10	22	0.4	22	Gray	44	76	1,200
OSM-A -25	N/A	25	55	1	55	Orange	44	76	1,200
OSM-A -50	70-OTHR0261	50	110	2	110	Red	44	76	1,200
OSM-A -100	70-OTHR0092	100	220	4	220	Blue	44	76	1,200
OSM-A -150	70-OTHR0043	150	330	6	330	Yellow	44	76	1,300
OSM-B -100	70-OTHR0057	100	220	4	220	Green	60	105	1,300
OSM-B -150	N/A	150	330	6	330	Brown	60	105	1,300
OSM-B -200	N/A	200	440	8	440	White	60	105	1,400
OSM-B -300	70-OTHR0188	300	660	12	660	Orange	60	105	1,400
OSM-B -400	N/A	400	880	16	880	Blue	60	105	1,500
OSM-C -350	N/A	350	770	14	770	Black	73	105	1,800
OSM-C -500	N/A	500	1100	20	1100	Green	73	105	2,000
OSM-C -600	N/A	600	1320	24	1320	Orange	73	105	2,200
OSM-C -750	N/A	750	1650	30	1650	Brown	73	105	2,300

SPRING แบบแขวน (USH)

MODEL	P/N	RATE CAP		MOUNT		SPRING			LIST PRICE
		KGS	LBS	KG / MM	LBS / INCH	COLOR CODE	OD	HT	
USH-A -10	N/A	10	22	0.4	22	Gray	44	76	1,200
USH-A -25	690411120001	25	55	1	55	Orange	44	76	1,200
USH-A -50	70-OTHR0211	50	110	2	110	Red	44	76	1,200
USH-A -100	70-OTHR0108	100	220	4	220	Blue	44	76	1,200
USH-A -150	70-OTHR0109	150	330	6	330	Yellow	44	76	1,300
USH-B -100	N/A	100	220	4	220	Green	60	105	1,800
USH-B -150	N/A	150	330	6	330	Brown	60	105	1,800
USH-B -200	70-OTHR0107	200	440	8	440	White	60	105	1,800
USH-B -300	N/A	300	660	12	660	Orange	60	105	1,900
USH-B -400	N/A	400	880	16	880	Blue	60	105	2,000
USH-C -350	N/A	350	770	14	770	Black	73	105	2,500
USH-C -500	N/A	500	1100	20	1100	Green	73	105	2,600
USH-C -600	N/A	600	1320	24	1320	Orange	73	105	2,800
USH-C -750	N/A	750	1650	30	1650	Brown	73	105	2,800