


LARGE COMMERCIAL

Split System 21-67 Tons RAUT/TTV R410A Series 50Hz








System Performance Matrix


Model		Evaporator Airflow	Total Capacity	Sensible Capacity	
Outdoor	Indoor	CFM MBH		MBH	
RAUT250	TTV250	6,600	245	167	
		7,760	250	177	
		9,050	258	190	
RAUT300	TTV300	7,900	294	190	
		9,240	300	214	
		10,600	309	227	
RAUT400	TTV400	10,300	392	272	
		12,120	400	288	
		13,900	412	306	
RAUT500	TTV500	12,900	491	345	
		15,130	500	365	
		17,400	515	389	
RAUT600	TTV600	15,400	589	425	
		18,080	600	450	
		20,800	618	480	
2xRAUT400	TTV800	20,600	785	544	
		24,240	800	576	
		27,800	824	612	

Notes : 1. Matching capacities based on ambient temperature of 95°F and 80/67°F air dry bulb/wet bulb entering the air handler coil. 2. Product design and specification are subject to change without notice.


Fan Arrangement




Arrangement 1 (Standa rd arrangement for TTV250-600)



Arrangement 2



Arrangement 3



Arrangement 4



General Data - Condensing Units

Model	Indoor Unit Outdoor Unit		TTV250	TTV300	TTV400	TTV500	TTV600	TTV800	
			RAUT250	RAUT300	RAUT400	RAUT500	RAUT600	2xRAUT400	
Performance Data	Nominal Cooling Capacity	Btu/h	250,000	300,000	400,000	500,000	600,000	800,000	
	Airflow	CFM	7,760	9,240	12,120	15,130	18,080	24,240	
Indoor Unit									
Electrical Data	Power Supply	V/ph/Hz	380-415/3/50						
No. of Refrigerant Circuit			2	2	2	2	2	2	
Expansion Device	Туре		Thermostatic Expansion Valve						
Fan	Туре		Forward Curve Centrifugal Fan						
	Qty		1	1	1	1	1	1	
Fan Motor	Output	Нр	5.5	7.5	7.5	10	15	20	
	RLA x Qty	A	8.6	12	12	15.2	22	29.6	
Pre-Filter	Туре		1-in Thickness Washable Aluminium						
Dimensions	H x W x D	mm	1,219x1,808x1,040	1,372x1,808x1,040	1,520x2,088x1,040	1,653x2,596x1,275	1,777x2,596x1,275	2,045x2,952x1,375	
Weight	Uncrated (net)	kg	353	421	487	685	749	900	
Refrigerant Pipe Size	Liquid	in	5/8	5/8	5/8	5/8	5/8	5/8	
	Suction	in	1-5/8	1-5/8	1-5/8	1-5/8	1-5/8	1-5/8	
Outdoor Units (per	each)								
Electrical Data	Power Supply	V/ph/Hz	380-415/3/50						
No. of Refrigerant Circuit			1	1	1	2	2	1	
Compressor	Туре		Hermetic Scroll						
	RLA x Qty	А	19.8 x 2	26.3 x 2	29.2 x 2	19.8 x 4	26.3 x 4	29.2 x 2	
Fan Motor	RLA x Qty	A	3.4 x 2	3.4 x 2	2.4 x 2	5.3 x 2	5.3 x 2	2.4 x 2	
Fan	Nominal Airflow	CFM	15,400	15,400	15,400	29,000	29,000	15,400	
Dimensions	H x W x D	mm	1,790 x 1,700 x 840		2,200 x 2,380 x 1,150		1,790 x 1,700 x 840		
Weight (Each)	Uncrated (net)	kg	345	360	400	860	890	400	
Piping Connnection Type			Brazed connection						
Refrigerant Pipe Size	Liquid	in	5/8	5/8	5/8	5/8	5/8	5/8	
	Suction	in	1-5/8	1-5/8	1-5/8	1-5/8	1-5/8	1-5/8	
Refrigerant			R410A						

<u>Note:</u> 1. Capacity is rated at ARI conditions of 80/67 °FDW/ °FWB for Indoor & 95 °FDB for Outdoor.
2. Unit dimensions depth does not include the dimensions of unit's legs.
3. Design and specification are subject to change without notice.

Product Specification

Condensing Units - RAUT Model

Standard Features

- Hermetic Scroll compressor.
- Microprocessor Controller with trouble shooting.
- Factory leak and pressure tested at 400 psig.
- Unit panels constructed of 0.9 mm. galvanized steel.
- Exterior panels are cleaned and then chemically treated and finished with a weather-resistant baked polyester powder paint.
 - Heavy gauge steel mounting/lifting rails under base.
 - Direct-drive, vertical discharge.
- 3-phase motors with permanently lubricated ball bearings.
- Utilization range of plus or minus 10 percent of the nameplate voltage.
- Condenser fan motor(s) built-in thermal overload protection.
 - Colored and numbered wiring.
 - Come with build-in under/over voltage and phase protection to prevent compressor damage from unstable electrical source.

Air Handling Units - TTV Model

Standard Features

- Vertical or Horizontal discharge configuration.
- Zinc coated, heavy gauge, galvanized steel cabinet finished with a baked polyester powder paint.
- Completely insulated with fire retardant polyethylene foam.
- Factory installed thermal expansion valve(s).
- Evaporator coil leak-tested.
- Double inlet, double width, forward curved centrifugal type evaporator fan(s) with fixed belt drive.
- Thermal overload protection for the evaporator fan motor.
- Washable air filters.
- Oversized motors for high static pressure applications (Optional).

Features Summary

High compressor EERs.

- Less vibration and a quieter operation
- Compressor Protection: External Overload Protector. External high and low pressure switches.
- Tandem Capability: Achieves high part load efficiencies and additional part load control.
- Oil charging valves.
- 3 Wire DOL Starter, minimizing field installation.

Trane Multi-Stage Thermostat controlled by microprocessor is available for 1, 2 and 4 stage monitor, 7-segment display, 15°C–30°C temperature setting, connectable with the external sensor & auto-restart function with ON/OFF switch.

Robust Casing

- Corrosion resistant coated coils as an option.Weather resistant baked matt polyester
- powder painted GI panels. Heavy gauge welded steel base with
- mounting holes.
- Aluminium blade propeller fans.
- Fully factory leak and pressure tested.

Micro Controller with labeled and numbered wiring.

- New PCB with 7-segment display is more user friendly and helpful to easily understand the code.
- Troubleshooting status display helps reduce service time.
- Higher reliability than traditional hard wired systems.

Option

Trane 1,2,4 Stage Thermostat provides with & without display, operation control of chilled water fan coil and AHU, 16°C - 30°C temperature setting, 4-level compressor monitor & display of compressor status.

Trane AHU Starter Panel particularly controls the HVAC system. Integrated with motor and compressor protection system, reliable according to UL/IEC/NEMA standard and easy to install.











©2022 Trane. All Rights Reserved. RAUT-EN June 22, 2022





Mirco processor controller





I, 2, 4 Stage Thermostat 1 or 2 Stage Digital Display (Option) Thermostat - Without Display (Option)



AHU Starter Panel (Option)