



# CONTURA 3G CASSETTE

---

## Minisplit Air Conditioners

### *Cassette Series*

*Underceiling Type*

*18,000-42,000 Btu/h*

*MCC & MWC Series*

*50/60 Hz*

*R22 & R407C*



## CONTURA 3G CASSETTE - Human Comfort Solutions



Trane is proud to present its new line of cassette-type minisplit air conditioners. Designed for recessed ceiling installation, this product will provide you with years of comfortable, convenient cooling, with minimal service required.

### Features

- **Fit all needs**
  - Available in 50 Hz and 60 Hz, cooling and heat pump.
  - Available in R22 and R407C.
- **Slim & Attractive Design**  
Trane's compact Cassette units feature a new and elegant design that enables more flexible installation, especially in a shallow ceiling pocket.

Cassette type air-conditioner serves not only as an air-conditioner but an indoor decoration as well, which makes it widely used in offices, stores and houses.

- **Ceiling Mounted Installation**  
Mounted in the ceiling, they leave the floor space uncluttered and free the interior designer from having to consider the air conditioner installation.



- **4-Way Directional Air Flow**

This multi-flow system features four different settings of the discharge outlets, offering many benefits:

- Provides wide vertical air distribution for better comfort, while cooling the entire room in a short period of time.
- Enhances down-flow performance and enables wide-range air-conditioning for medium discharge.
- Enables adjustment of the airflow direction to reduce air resistance.
- Quiet operation: high efficiency with low noise levels.



**MCC518BB**




**MCC524BB**



**MCC536BB, MCC542BB**




Indoor Unit





Model	D	H
MCC518/MWC518	220	190
MCC524/MWC524	270	240
MCC536/MWC536	355	320
MCC542/MWC542	355	320

Unit: mm



LCD Wireless Remote Control



- Provides maximum convenience.
- **Fan Speed:** allows for automatic control of four fan settings: High, Medium, Low or Automatic.
- **Mode of Operation:** allows for selection of the operating mode: Fan, Cool, Heat (for cooling & heating system), Dry, Sleep or Auto.
- **Temperature Setting:** between 16°C-30°C.
- **24-Hour Programmable Timer:** allows you to preset the times for system operation, up to 24-hours in advance.
- **Louver and Sweep Mode:** allows for control of the air flow direction and improved air circulation.
- **Sleep Mode:** automatic temperature adjustment for more comfortable sleeping conditions and energy savings.
- **Dry Mode:** controls humidity and maintains a constant temperature, while saving energy.

• **Auto Recovery Function:** **New!**

In case of power interruption, the control will resume its operation automatically with the same setting parameters such as mode, swing, temperature setting, and fan speed setting.

**Quality**

Trane Air Conditioners are designed and constructed to provide long life and trouble-free system.

All major components are individually inspected and tested, and every unit undergoes a run-test, prior to shipment from the factory.

**High Efficiency Condensing Unit**

- Compact in size for easy installation into small spaces.
- Galvanized steel with a Silver-Gray powder paint finish for corrosion resistance.



TTK518ZB



TTK524ZB



TTK536ZD, TTK542ZD

