



TRANE®

Information requirements for comfort chillers

Model(s):	GVWF 325 - R134a
Outdoor side heat exchanger of chiller:	water/brine
Indoor side heat exchanger of chiller:	water
Type:	compressor driven vapour compression
Driver of compressor:	electric motor

Item	Symbol	Value	Unit	Item	Symbol	Value	Unit
Rated cooling capacity	$P_{rated,c}$	1 088.0	kW	Seasonal space cooling energy efficiency	$\eta_{s,c}$	335.0	%
Declared cooling capacity for part load at given outdoor temperatures Tj				Declared energy efficiency ratio or gas utilisation efficiency/auxiliary energy factor for part load at given outdoor temperatures Tj			
T j = +35 °C	P_{dc}	1088.0	kW	T j = +35 °C	EER_d	5.6	kW/kW
T j = +30 °C	P_{dc}	825.0	kW	T j = +30 °C	EER_d	7.4	kW/kW
T j = +25 °C	P_{dc}	524.0	kW	T j = +25 °C	EER_d	9.1	kW/kW
T j = +20 °C	P_{dc}	232.0	kW	T j = +20 °C	EER_d	11.0	kW/kW
Degradation co-efficient for chillers (*)	C_{dc}	0.0	—				

Power consumption in modes other than 'active mode'

Off mode	P_{OFF}	0.000	kW	Crankcase heater mode	P_{CK}	0.000	kW
Thermostat-off mode	P_{TO}	0.540	kW	Standby mode	P_{SB}	0.160	kW

Other items

Capacity control	Variable			For air-to-water comfort chillers: air flow rate, outdoor measured	—	NA	m ³ /h
Sound power level, outdoor	L_{WA}	-	dB(A)	For water/brine-to-water chillers: Rated brine or water flow rate, outdoor side heat exchanger	—	225	m ³ /h
GWP of the refrigerant		1 430	kg CO2 eq (100 years)				

Standard rating conditions used: low temperature application

Contact details: TRANE 88190 Golbey - France

(*) If C_{dc} is not determined by measurement then the default degradation coefficient of chillers shall be 0,9.