



TRANE®



DDHA

*Direct Drive Air Handling Unit
2,000-8,000 CFM 50 Hz*

DDHA – Air handling Unit with direct drive motor

AHU with direct drive fan motor specially designed for free blow or short duct application to meet market requirement with low noise and smooth operation. Easy control and operate the AHU without the need of AHU starter.

Unit Casing

Units casing is constructed of zinc coated, heavy gauge, galvanized steel. Exterior surface is cleaned, phosphatized and finished with a polyester powder painted and weather resistant baked enamel finish. Casing is complete insulated with fire-retardant, permanent, odorless polyethylene foam.



DDHA Unit



Direct Drive Motor

Fans

Fans are double width, double inlet, multiblades centrifugal type. All fans are statically and dynamically balanced and tested from factory.

Coils

Configured aluminum fin surface is mechanically bonded to internally enhanced copper tubing with factory pressure and leak tested at 380 psig. Coil is arranged for draw trough airflow and shall provide full condensate drain pan constructed of galvanized steel with enough insulation thickness to prevent condensation.

Fan Motor

3-speed fan motor with direct drive type is provided for ease of control and operation. Thermostat with

control desired fan speed at high, medium or low speed.

Trane Thermostat (Option)

Digital room thermostat with 3 speeds fan adjustment and ON/OFF switch. Temperature setting can be adjusted from 18-30 °C with 7-segment LED display and auto restart function.



Product Specification

MODEL	DDHA20	DDHA25	DDHA34	DDHA40
Rated - Volts/Ph/Hz	220-240/1/50	220-240/1/50	220-240/1/50	220-240/1/50
SYSTEM DATA				
Nominal Airflow	CFM 2,000	2,500	3,400	4,000
Nominal Capacity	MBH 60	75	100	120
Water Inlet Connection Size	in 1 1/4	1 1/4	1 1/4	1 1/2
Water Outlet Connection Size	in 1 1/4	1 1/4	1 1/4	1 1/2
Water Connection Type	Steel Pipe - MPT			
COIL				
Fin Type	Uncoated Corrugate			
Fins per inch*				
3-Row coil	14	14	14	14
4-Row coil	12	13	14	13
Drain Connection Size	in 1	1	1	1
FAN				
Fan Type	Double Inlet Centrifugal Forward Curved Wheel			
Qty	1	1	2	2
Drive Type	Direct Drive			
FAN MOTOR				
Motor Type	Permanent Split Capacitor			
Qty x RLA	1 x 2.02	1 x 2.82	2 x 2.02	2 x 2.19
No. of Speed	3	3	3	3
RETURN FILTER				
Filter Type	Washable Air Filter			
DIMENSION (HxWxD)				
Unit (Net)	mm 548 x 1,461 x 765	548 x 1,461 x 765	548 x 1,830 x 765	548 x 1,830 x 765
WEIGHT				
Unit (Net) 3-Row Coil	kg 87	91	137	142
Unit (Net) 4-Row Coil	kg 89	95	143	149

TC = Total Capacity, MBH
 SC = Sensible Capacity, MBH
 GPM = Water Flow Rate, gpm
 PD = Water Pressure Drop, Ft of Water
 EWT = Entering Water Temperature
 WTR = Water Temperature Rise

Cooling Capacity for 3-Row Coil

EWT (F)	Unit Size	Rated Airflow CFM	WTR (F)	Entering Air Temp - EDB/EWB (F)															
				72 /61				74 /63				80 /67				84 /71			
				TC	SC	GPM	PD	TC	SC	GPM	PD	TC	SC	GPM	PD	TC	SC	GPM	PD
45	20	2000	8	40.92	35.57	10.19	4.50	48.77	38.00	12.15	6.11	68.01	47.41	16.94	10.90	89.99	53.34	22.39	17.76
			10	35.70	33.44	7.11	2.40	42.88	35.63	8.55	3.30	61.49	44.85	12.25	6.17	82.82	50.60	16.51	10.37
			12	30.03	28.67	4.99	1.29	36.64	33.20	6.09	1.82	55.07	42.38	1.95	3.69	75.33	47.78	12.51	6.36
			15	17.59	17.36	2.34	0.35	25.21	24.82	3.35	0.64	44.87	38.63	5.97	1.74	63.75	43.62	8.47	3.21
	25	2500	8	50.02	43.67	12.46	7.06	59.28	46.55	14.77	9.49	82.33	57.94	20.51	16.83	108.50	65.05	27.02	27.31
			10	44.49	41.42	8.87	3.89	52.88	43.97	10.54	5.25	75.21	54.90	15.04	9.57	100.20	61.85	19.98	16.01
			12	38.69	36.97	6.43	2.22	46.38	41.39	7.70	3.03	67.63	52.19	11.23	5.83	91.53	58.54	15.20	9.88
			15	28.15	27.78	3.74	0.86	35.62	33.88	4.74	1.30	56.97	48.20	7.57	2.92	78.73	53.87	10.47	5.12
	34	3400	8	67.76	60.17	16.88	7.13	80.05	64.23	19.94	9.54	110.10	80.20	27.42	16.62	143.90	90.31	35.85	26.58
			10	60.00	56.92	11.96	3.90	71.31	60.57	14.21	5.26	100.30	76.03	19.94	9.48	133.20	85.88	26.54	15.62
			12	51.48	50.13	8.55	2.17	62.02	56.85	10.30	3.00	90.52	72.23	15.04	5.77	121.70	81.34	20.22	9.67
			15	25.71	25.49	3.43	0.44	44.43	44.30	5.91	1.14	75.43	66.37	10.03	2.84	104.60	74.78	13.91	5.00
40	4000	8	82.22	73.30	20.48	5.51	97.00	78.16	24.16	7.35	132.80	97.30	33.08	12.71	173.60	109.41	43.23	20.30	
		10	72.43	69.18	14.44	2.99	86.16	73.65	17.17	4.04	121.00	92.44	24.12	7.29	160.40	104.03	31.97	11.91	
		12	61.44	59.85	10.21	1.63	74.36	68.92	12.35	2.27	109.30	87.75	18.16	4.43	146.50	98.52	24.34	7.37	
		15	31.95	30.38	4.25	0.36	53.28	52.08	7.10	0.93	90.19	80.38	11.99	2.14	125.70	90.62	16.71	3.80	



Trane optimizes the performance of home and buildings around the world. A business of Ingersoll Rand, the leader in creating and sustaining safe, comfortable, and energy efficient environments, Trane offers a broad portfolio of advance controls and HVAC systems, comprehensive building services, and parts. For more information, visit www.tranethailand.com

ทราน (ประเทศไทย)

เลขที่ 1126/2 ชั้น 30-31 อาคารวานิช 2 ถ.เพชรบุรีตัดใหม่ แขวงมักกะสัน เขตราชเทวี กรุงเทพฯ 10400

☎ 0-2761-1111

© 2018 Trane All rights reserved

DDHA-SLS001-EN January 11, 2018

