



CONTURA
High Wall Mini-Split
9,000-36,000 BTU
MCW Series

Standard Indoor Units
 Specifications: 200-240/1/50 or 220/-240/1/60

Model	Cooling Capacity (BTU)	Airflow (60 Hz) CFM CMH		Dimensions						Weight lb. kg.	
				Height		Width		Depth			
				in	mm	in	mm	in	mm		
MCW509K	9,000	225	380	9.8	252	30.3	770	7.1	180	18.7	8.5
MXW512K	12,000	265	450	9.8	252	30.3	770	7.1	180	18.7	8.5
MCW518K	18,000	412	700	11.4	290	35.7	907	7.7	195	26.4	12
MCW524K	24,000	425	720	11.4	290	35.7	907	7.7	195	26.4	12
MWW536K	36,000	825	1401	14	365	57	1450	8.5	215	54	24.5