



# CASSETTE

## Chilled Water Coil

*Cassette Series*  
*Underceiling Type*  
*9,000-40,000 Btu*  
*CWS Series 50 Hz*



# CASSETTE - Chilled Water Coil

Trane is proud to present it's the elegant design of cassette chilled water coil. This water coil is carefully manufactured according to Trane Worldwide Quality Standards to provide you years of comfort, convenient cooling with minimal service required.

## Elegant Design

- 4-way airflow that can distribute cool air throughout the room
- Do not disturb your relaxation due to its low noise operation

## Electrostatic Air Filter (Option)

Provide you better air cleanliness that good for your health by removing dusts, odors, and micro-organism from the air.



## Digital Control

With handheld wireless remote, you can have all control just at your fingers.

- **4-fan speeds control** - Hi, Me, Lo and Auto
- **24-Hour programmable timer** - set time to automatically turn on or turn off
- **Louver and Sweep Mode** - help distribute airflow efficiently throughout the room
- **Turbo Mode** - help accelerate cooling capacity in the room

## Specifications

Model	CFM	EWT (Deg F)	Cooling Capacity		Gpm	Pressure Drop (Ft of Water)	Dimension (mm)	
			Total MBH	Sensible MBH			Housing (H x W x D)	Front Panel (H x W x D)
CWS 03	300	40	11.23	7.861	2.235	1.90	310x570x570	40x720x720
		45	8.63	6.678	1.712	1.60		
		50	6.14	5.312	1.220	1.10		
CWS 04	400	40	15.08	10.535	2.996	3.70	310x570x570	40x720x720
		45	12.04	9.190	2.393	3.30		
		50	9.04	7.670	1.807	2.10		
CWS 06	600	40	24.16	15.702	4.803	17.00	290x830x830	80x950x950
		45	19.52	13.682	3.883	11.10		
		50	14.84	11.648	2.964	6.80		
CWS 08	800	40	30.19	19.412	6.007	19.20	290x830x830	80x950x950
		45	24.49	16.915	4.882	17.10		
		50	18.69	14.425	3.725	9.10		
CWS 10	1,000	40	38.15	24.466	7.592	10.10	340x830x830	80x950x950
		45	30.88	21.236	6.182	7.50		
		50	23.78	18.237	4.739	6.80		
CWS 12	1,200	40	45.45	28.597	9.035	12.40	340x830x830	80x950x950
		45	37.19	24.910	7.402	11.20		
		50	28.63	21.266	5.706	8.87		
CWS 14	1,200	40	51.18	32.790	10.190	13.00	340x830x830	80x950x950
		45	40.01	27.990	8.000	8.21		
		50	28.67	23.740	5.720	4.58		

Note : Rating are based on 10 deg F water temperature rise and entering air temperature is 80 FDB / 67 FWB



Trane Thailand  
1126/2, 30<sup>th</sup>-31<sup>st</sup> Floor, Vanit Building II,  
New Petchburi Road, Makkasan,  
Rachthevee, Bangkok 10400

Amair Limited  
999/1 Mu 9, Bangna-Trad Km. 19 Road, Bangchalong,  
Bangplee, Samutprakarn Bangkok 10540

<http://www.tranethailand.com>

Literature Order Number: UNT-SLB-CWS

Date: Sep 2012

Supersedes: Feb 2009

Stocking Location: Bangkok, Thailand

Trane has a policy of continuous product and product data improvement and reserves the right to change design and specifications without notice.