



TRANE®

RTAC 355 XE LN

<-

Select the unit

Information requirements for comfort chillers

Model(s):	RTAC 355 XE LN
Outdoor side heat exchanger of chiller:	Air
Indoor side heat exchanger of chiller:	Water
Type:	compressor driven vapour compression
Driver of compressor:	electric motor

Item	Symbol	Value	Unit	Item	Symbol	Value	Unit
Rated cooling capacity	$P_{rated,c}$	1 237.2	kW	Seasonal space cooling energy efficiency	$\eta_{s,c}$	167.7	%
Declared cooling capacity for part load at given outdoor temperatures T_j				Declared energy efficiency ratio or gas utilisation efficiency/auxiliary energy factor for part load at given outdoor temperatures T_j			
$T_j = +35\text{ °C}$	P_{dc}	1237.2	kW	$T_j = +35\text{ °C}$	EER_d	2.9	kW/kW
$T_j = +30\text{ °C}$	P_{dc}	910.0	kW	$T_j = +30\text{ °C}$	EER_d	3.7	kW/kW
$T_j = +25\text{ °C}$	P_{dc}	583.8	kW	$T_j = +25\text{ °C}$	EER_d	4.7	kW/kW
$T_j = +20\text{ °C}$	P_{dc}	260.5	kW	$T_j = +20\text{ °C}$	EER_d	5.0	kW/kW
Degradation co-efficient for chillers (*)	C_{dc}	0.9	—				

Power consumption in modes other than 'active mode'

Off mode	P_{OFF}	0.000	kW	Crankcase heater mode	P_{CX}	0.935	kW
Thermostat-off mode	P_{TO}	2.635	kW	Standby mode	P_{SB}	0.935	kW

Other items

Capacity control	variable			For air-to-water comfort chillers: air flow rate, outdoor measured	—	307994	m ³ /h
Sound power level, outdoor	L_{WA}	95.0	dB(A)	For water/brine-to-water chillers: Rated brine or water flow rate, outdoor side heat exchanger	—	NA	m ³ /h
GWP of the refrigerant		1 340	kg CO ₂ eq (100 years)				

Standard rating conditions used: 0

Contact details TRANE 88190 Golbey - France

(*) If C_{dc} is not determined by measurement then the default degradation coefficient of chillers shall be 0,9