



TRANE®

Technical parameters for heat pump space heaters and heat pump combination heaters

Model(s): [information identifying the model(s) to which the information relates]	RTWF100HE+Heating+VFD
Air-to-water heat pump:	No
Water-to-water heat pump:	Yes
Brine-to-water heat pump:	No
Low-temperature heat pump:	No
Equipped with a supplementary heater:	No
Heat pump combination heater:	No
Parameters shall be declared for medium-temperature application, except for low-temperature heat pumps. For low-temperature heat pumps, parameters shall be declared for low-temperature application.	
Parameters shall be declared for average, colder and warmer climate conditions.	

Item	Symbol	Value	Unit	Item	Symbol	Value	Unit
Rated heat output (*)	Prated	376	kW	Seasonal space heating energy efficiency	η_s	2	%
Declared capacity for heating for part load at indoor temperature 20 °C and outdoor temperature T j				Declared coefficient of performance or primary energy ratio for part load at indoor temperature 20 °C and outdoor temperature T j			
T j = - 7 °C	Pdh	331.7	kW	T j = - 7 °C	COPd or PERd	3.69	- or %
T j = + 2 °C	Pdh	201.8	kW	T j = + 2 °C	COPd or PERd	4.65	- or %
T j = + 7 °C	Pdh	130.2	kW	T j = + 7 °C	COPd or PERd	4.98	- or %
T j = + 12 °C	Pdh	57.7	kW	T j = + 12 °C	COPd or PERd	6.05	- or %
T j = bivalent temperature	Pdh	375.5	kW	T j = bivalent temperature	COPd or PERd	3.50	- or %
T j = operation limit temperature	Pdh	375.5	kW	T j = operation limit temperature	COPd or PERd	3.50	- or %
For air-to-water heat pumps: T j = - 15 °C (if TOL < - 20 °C)	Pdh	-	kW	For air-to-water heat pumps: T j = - 15 °C (if TOL < - 20 °C)	COPd or PERd	-	- or %
Bivalent temperature	T biv	-10	°C	For air-to-water heat pumps: Operation limit temperature	TOL	-	°C
Cycling interval capacity for heating	Pcyc	-	kW	Cycling interval efficiency	COPcyc or PERcyc	0.94	- or %
Degradation co-efficient (**)	Cdh	-	-	Heating water operating limit temperature	WTOL	68.00	°C
Power consumption in modes other than active mode				Supplementary heater			
Off mode	P OFF	0.00	kW	Rated heat output (*)	Psup	0.00	kW
Thermostat-off mode	P TO	0.73	kW	Type of energy input	Electricity		
Standby mode	P SB	0.55	kW				
Crankcase heater mode	P CK	0.55	kW				
Other items				For air-to-water heat pumps: Rated air flow rate, outdoors			
Capacity control	Variable			For water-/brine-to-water heat pumps: Rated brine or water flow rate, outdoor heat exchanger			
Sound power level, indoors/ outdoors	LWA	#REF!	dB				
Annual energy consumption	QHE	169085	kWh				
Declared load profile				Water heating energy efficiency			
Average				η_{wh}			
Daily electricity consumption	Q elec			Daily fuel consumption			
Annual electricity consumption	AEC	-	kWh	Annual fuel consumption			
				AFC			
Contact details	TRANE 88190 Golbey - France						

(*) For heat pump space heaters and heat pump combination heaters, the rated heat output Prated is equal to the design load for heating Pdesignh, and the rated heat output of a supplementary heater Psup is equal to the supplementary capacity for heating sup(Tj). (**) If Cdh is not determined by measurement then the default degradation coefficient is Cdh = 0,9.