



TRANE®



Let's Go Beyond
Trane Canada (East)
Products and Solutions Line Card



Trane® Control Systems



Tracer® ES™

Enterprise wide/multi-building management cloud based solution



Tracer® SC

Scalable web-based building automation solution



Tracer® Concierge™

Bundled Building & Lighting Controls



Tracer® Equipment Controls

Factory & Field Mounted Equipment Controllers. Easily integrate with other protocols



Trane Drives

Trane TR150/TR200 Variable Frequency Drives; 6, 12, & 18 Pulse



Trane Prepackaged Solutions (PPS)

Complete portfolio of pre-designed HVAC systems controls solutions that make planning, specifying, schematics and incorporating Trane control systems fast and efficient



BAS R'Newal™

Controls Program Upgrade

Trane® Energy Management Systems & Services



Trane Intelligent Services

Aggregates data collected in a building. Provides tools to make real-time, near-term, and long-term decisions that maximized the way buildings are managed and maintained

EarthWise™ Solutions



Prepackaged Equipment & Controls. Intelligent VAV, Thermal Ice Storage, Central Geothermal, Low Temp/Low Flow

Water-Cooled Chillers



Model CICB

Scroll Chiller, 30 ton capacity, expandable 10x. Nominal 15 HP/circuit, ASHRAE 90.1-2013 compliant



Model CGWQ

Scroll Compressors - 20 thru 70 tons



Series R Model RTWD

Helical Rotary Compressor - 80 thru 250 tons



Series R Model RTHD

Helical Rotary Compressor - 150 thru 450 tons



Optimus™ Model RTHD

Variable Speed Helical Rotary Compressor - 150 thru 450 tons



Series S Model CVHS

CentraVac® Chiller - Oil-Free Centrifugal Compressor - 180 thru 390 tons



Model CVHE CentraVac Chiller

3-Stage Centrifugal Compressor - 120 thru 500 tons



Model CVHF CentraVac Chiller

2-Stage Centrifugal Compressor - 325 thru 2,000 tons



Model CVHL CentraVac Chiller

Centrifugal Compressor for Elevated Chilled Water Temperatures - 400 thru 1,800 tons



Model CDHF CentraVac Chiller

Dual Compressor Centrifugal Compressor - 1,500 thru 4,000+ tons

Air-Cooled Chillers



Model CCAQ

Scroll Compressor with Air-Cooled Condenser; 20 thru 70 tons



Model RTUD

Helical Rotary Compressor with Air-Cooled Condenser - 80 thru 250 tons



Model CGAM

Scroll Compressor - 20 thru 130 tons



Series R RTAC

Helical Rotary Chiller - 140 thru 500 tons



Stealth™ Model RTAE

Variable Speed Helical Rotary Compressor - 150 thru 300 tons



Sintesis™ Model

Variable Speed Helical Rotary Compressor - 110 thru 500 tons

Air Handling Systems



Blower Coil Model BCHD/BCVD

Indoor; 400 thru 3,000 CFM; ECM motors; Factory-Engineered & Mounted Controls



Performance Climate Changer™ Model UCCA

Indoor; 1,500 thru 15,000 CFM; 2" R-13 Foam Insulated Panels; Factory-Engineered & Mounted Controls



Performance Climate Changer™ Model CSAA

Indoor & Outdoor; 1,500 thru 60,000 CFM; 2" R-13 Foam Insulated Panels; Factory-Engineered & Mounted Controls

Terminal Products



Model VUVE

Vertical Unit Ventilators; 750 thru 1,500 CFM



Model HUVU

Horizontal Unit Ventilators; 750 thru 2,000 CFM



UniTrane™ Model FC*B

FAN COIL; 200 THRU 1,200 CFM



Force-Flo™ Model FF*B

Cabinet Heater; 200 thru 1,200 CFM



VariTrane™ Model VC*F

Single Duct Variable Air Volume Boxes; 225 thru 8,000 CFM



VariTrane™ Model VDDF

Dual Duct Variable Air Volume Boxes; 350 thru 4,000 CFM



VariTrane™ Model V**F

Fan-Powered Variable Air Volume Boxes; 350 thru 4,000 CFM; Parallel or Series Configuration



VariTrane™ Model L**F

Low Height Fan-Powered Variable Air Volume Boxes; 350 thru 4,000 CFM; Parallel or Series Configuration



VariTrane™ Model VRRF

Round Inlet/Round Outlet RetroFit Variable Air Volume Boxes; 225 thru 4,000 CFM



Model UHS/UHP

Propeller Unit Heaters; Hydronic & Steam



Model UHWA/UHAA/UHRA/UHXA/UHEC/UHCA

Electric Unit Heaters



Indoor Gas Heating Units

Unit Heaters & Duct Furnaces

Packaged Rooftops



Impack®

Cooling, Gas/Electric, and Heat Pump; 1.5 thru 5 tons



Precedent™ 17 Plus Packaged Rooftops

Cooling & Gas/Electric; 17 SEER; 3 thru 5 tons



Precedent™ & Precedent eFlex™

Cooling & Gas/Electric, Air-Source or Water-Source Heat Pump; eFlex Variable Speed Compressor; 3 thru 10 tons



Voyager™ & Voyager eFlex™

Cooling & Gas/Electric, Air-Source or Water-Source Heat Pump; eFlex Variable Speed Compressor; 12.5 thru 17.5 tons



Foundation™

Cooling, Gas/Electric; Adapts to trane and Competitors Roof Curbs; 12.5 thru 25 tons



Voyager Commercial

Cooling, Gas/Electric; 27.5 thru 50 tons



IntelliPak™ I

Cooling, Gas/Electric, Hot Water, Steam; 20 thru 75 tons



IntelliPak™ II

Cooling, Gas/Electric, Hot Water, Steam; Air-Cooled and Evaporative Condenser; 90 thru 162 tons

Dedicated Outdoor Air Rooftops



Horizon™ Model OA

Packaged Outdoor Air Units; Cooling, Gas/Electric, Air-Source or Water-Source Heat Pump; Heat Recovery; 500 thru 13,500 CFM

Make-Up Air Gas Heating Units



Model DFIA/DFOA

Direct Fired Make-Up Air Units; Indoor & Outdoor; 225 thru 9,075 MBH



Model GSAA

Indoor Gas-Fired Make-Up Air Handlers; Standard & High Efficiency; 100 thru 1,200 MBH



Model GRAA

Outdoor Gas-Fired Make-Up Air Handlers; 100 thru 1,200 MBH



Model AHOA

Packaged Air Handlers; Cooling, Make-Up Air & Ventilation

Split Systems



Split Systems

Cooling & Heat Pump; Gas, Electric, or Hot Water Heat; 1.5 thru 5 tons



Odyssey™ Split Systems

Cooling & Heat Pump; Electric, Hot Water, Steam Heat; 6 thru 25 tons



Model RAUJ

Air-Cooled Condensing Units; Available with Remote Chiller Evaporators; 20 thru 120 tons



Model CAUJ

Air-Cooled Condensers 20 thru 120 tons

Ductless Split Systems



Ductless Split Systems

Cooling only, Heat Pump, Single Zone, Multizone; Up to 27 SEER, Up to 38.2 IEER



Trane VRF

Variable Refrigerant Volume; Heat Pump & Heat Recovery Option; 3 thru 36 tons

Self-Contained Systems



IntelliPak™ Modular Series

Water-Cooled or Air-Cooled; 20 thru 25 tons



IntelliPak™ Signature Series

20 thru 110 tons (Water-Cooled); 20 thru 60 tons (Air-Cooled)



Midrange

Water-Cooled, Remote Air-Cooled, or Integral Air-Cooled; 3 thru 15 tons

Water-Source Heat Pumps



Axiom™ Model GEH/GEV

1/2 thru 15 tons (Horizontal); 1/2 thru 25 tons (Vertical)



Axiom™ Model EXH/EXV

High-Efficiency; ECM Motors; 1.5 thru 6 tons



Axiom™ Model DXH/DXV

High-Efficiency 2-Stage; ECM Motors; 2-Stage Compressor; 2 thru 6



Axiom™ Model VSH/VSV

High-Efficiency Variable Speed; ECM Motors; Variable Speed Compressor; 2 thru 5 tons



Axiom™ Model GEC

High-Efficiency Console; 1/2 thru 1.5 tons



Axiom™ Model GET

High-Efficiency Vertical Stack; 3/4 thru 3 tons



Axiom™ Model EXW

Water to Water 5 thru 20 tons

Trane Rental Services



Water-Cooled Chillers, Air-Cooled Chillers, Temporary Power, Cooling Towers, Packaged A/C Units, Air Handlers, Portable A/C Units

Trane Canada (East) - Atlantic Region Represented Products



Aldes
www.aldes.ca
ERVs



BKM
www.reverse-flow.com
Reverse Flow HRVs



Calmac
www.calmac.com
Ice Storage & Controls



Danfoss
www.danfoss.us
AC Units



Desert Aire
www.desert-aire.com
Dehumidifiers



driSteem
www.dristeem.com
Humidifiers



DryAir
www.dryair.ca
Heating & Thawing Solutions



Dynamic
www.dynamicaqs.com
Filters



Fantech
www.fantech.net
HRVs



Gunter
www.guntner.us
Coolers & Condensers



Haakon Industries
www.haakon.com
Custom Air Handling Units



Indeeco
www.indeeco.com
Electric Heating



Kampmann
www.kampmann.ca
Trench Heating



KCC
www.kccmfg.com
Roof Curbs & Adapters



Krueger
www.krueger-hvac.com
VAV, Diffusers & Grilles



LJ Wing
www.ljwing.com
HVAC Components




Mestek
www.mestek.com
HVAC Systems



Miller Leaman
www.millerleaman.com
Filters & Strainers



Motivair
www.motivaircorp.com
Heat Pumps & Chillers



Multistack
www.multistack.com
Chillers & Modular Systems



PennBarry
www.pennbarry.com
Fans



Trane Canada (East) - Atlantic Region Represented Products



Rupp Air
www.ruppams.com
Make-Up Air Systems



SPX / Marley
www.spxcooling.com
Heat Exchangers



SWEP
www.swep.net
Heat Exchangers



System Air
www.systemair.com
ERVs & Specialty Air
Products



Temprite
www.tempriteheating.com
Climate Control Sys-
tems



Thermax
www.thermax-usa.com
Absorption Chillers



Thermolec
www.thermolec.com
Coils



Thermotech
www.thermotech-usa.com
Heat Wheels



Thybar
www.thybar.com
Roof Curbs



United Cool Air
www.unitedcoolair.com
Modular Systems



VAW Systems
www.vawsystems.com
Silencers, Filters &
Plenums

Visit Trane.com/Atlantic, or call **866.338.7263** to learn more.

Halifax/Dartmouth
250 Brownlow Ave, Unit 4
Dartmouth, NS B3B 1W9
902.835.7491

Saint John
120 McDonald St., Suite G
Saint John, NB E2J 1M5
506.633.2300

Mount Pearl
22 Beclin Rd
Mount Pearl, NL A1N 5B8
709.753.8678

Trane Canada (East) - Atlantic Region

Halifax/Dartmouth

250 Brownlow Ave., Unit 4
Dartmouth, NS B3B 1W9
902.835.7491

Saint John

120 McDonald St., Suite G
Saint John, NB E2J 1M5
506.633.2300

Mount Pearl

22 Beclin Rd.
Mount Pearl, NL A1N 5B8
709.753.8678

Visit Trane.com/Atlantic to learn more.



Ingersoll Rand (NYSE:IR) advances the quality of life by creating and sustaining safe, comfortable and efficient environments. Our people and our family of brands — including Club Car®, Ingersoll Rand®, Thermo King® and Trane® — work together to enhance the quality and comfort of air in homes and buildings; transport and protect food and perishables; secure homes and commercial properties; and increase industrial productivity and efficiency. We are a \$13 billion global business committed to a world of sustainable progress and enduring results.



trane.com

ingersollrand.com