


Product Data

Split System Cooling


4TTR3018N1000A 4TTR3024N1000A 4TTR3030N1000A 4TTR3030N1000B 4TTR3036N1000A 4TTR3042N1000A 4TTR3048N1000A 4TTR3060N1000A







Outline Drawing



| Model | Base | Α | В | С | D | Е | F | G | Н | J | K |
|-----------|------|-----------------|-----------------|-----------------|-----|-----|----------------|---------------|----------------|---------------|-------------|
| 4TTR3018N | 2 | 730 (28-3/4) | 724 (28-1/2) | 651 (25-5/8) | 3/4 | 3/8 | 127 (5) | 57 (2-1/4) | 194 (7-5/8) | 38 (1-1/2) | 457 (18) |
| 4TTR3024N | 2 | 730 (28-3/4) | 724 (28-1/2) | 651 (25-5/8) | 3/4 | 3/8 | 127 (5) | 57 (2-1/4) | 194 (7-5/8) | 38 (1-1/2) | 457 (18) |
| 4TTR3030N | 3 | 730 (28-3/4) | 829 (32-5/8) | 756 (29-3/4) | 3/4 | 3/8 | 127 (5) | 76 (3) | 197 (7-3/4) | 60 (2-3/8) | 508 (20) |
| 4TTR3036N | 3 | 730 (28-3/4) | 829 (32-5/8) | 756 (29-3/4) | 3/4 | 3/8 | 127 (5) | 76 (3) | 197 (7-3/4) | 60 (2-3/8) | 508 (20) |
| 4TTR3042N | 4 | 741 (29-1/8) | 946 (37-1/4) | 870 (34-1/4) | 7/8 | 3/8 | 143 (5-5/8) | 83 (3-1/4) | 206 (8-1/8) | 70 (2-3/4) | 508 (20) |
| 4TTR3048N | 4 | 741 (29-1/8) | 946 (37-1/4) | 870 (34-1/4) | 7/8 | 3/8 | 143 (5-5/8) | 83 (3-1/4) | 206 (8-1/8) | 70 (2-3/4) | 508 (20) |
| 4TTR3060N | 4 | 943 (37-1/8) | 946 (37-1/4) | 870 (34-1/4) | 7/8 | 3/8 | 152 (6) | 98 (3-7/8) | 219 (8-5/8) | 86 (3-3/8) | 508 (20) |



Product Specifications

| Model No. (a) | 4TTR3018N1000A | 4TTR3024N1000A | 4TTR3030N1000A/B | 4TTR3036N1000A | |
|---|---------------------|---------------------|----------------------------|---------------------|--|
| POWER CONNS V/PH/HZ (b) | 208/230/1/60 | 208/230/1/60 | 208/230/1/60 | 208/230/1/60 | |
| MIN. BRCH. CIR. AMPACITY | 12 | 12 | 17 / 14 | 16 | |
| BR. CIR. PROT. RTG MAX. (AMPS) | 20 | 20 | 25 | 25 | |
| COMPRESSOR | CLIMATUFF® - SCROLL | CLIMATUFF® - SCROLL | CLIMATUFF® - SCROLL | CLIMATUFF® - SCROLL | |
| RL AMPS – LR AMPS | 9 – 63 | 10.1 - 52 | 12.8 - 68 / 10.9 - 62.6 | 12.2 - 80.1 | |
| Outdoor Fan FL AMPS | 0.9 | 0.9 | 0.77 | 0.77 | |
| Fan HP | 1/8 | 1/8 | 1/8 | 1/8 | |
| Fan Dia (inches) | 18.2 | 18.2 | 23 | 23 | |
| Coil | SPINE FIN™ | SPINE FIN™ | SPINE FIN™ | SPINE FIN™ | |
| Refrigerant R-410A | 4 LBS., 11 OZ | 4 LBS., 15 OZ | 4 LBS., 11 OZ | 5 LBS., 2 OZ | |
| VALVE CONNECTION SIZE - IN. O.D. GAS | 3/4 | 3/4 | 3/4 | 3/4 | |
| VALVE CONNECTION SIZE - IN. O.D. LIQ | 3/8 | 3/8 | 3/8 | 3/8 | |
| LINE SIZE – IN. O.D. GAS (c) | 3/4 | 3/4 | 3/4 | 3/4 | |
| LINE SIZE – IN. O.D. LIQ. (c) | 3/8 | 3/8 | 3/8 | 3/8 | |
| Charge Spec. Subcooling | 10°F | 10°F | 10°F | 10°F | |
| Dimensions H x W X D Crated (IN.) | 30.1 x 26.7 x 30 | 30.1 x 26.7 x 30 | 34 x 30.1 x 33 | 34 x 30.1 x 33 | |
| Weight - Shipping (lbs.) | 153 | 153 | 183 | 189 | |
| Weight - Net (lbs.) | 133 | 133 | 156 | 161 | |
| Optional Accessories: | | | | | |
| Anti-short Cycle Timer | TAYASCT501A | TAYASCT501A | TAYASCT501A | TAYASCT501A | |
| Evaporator Defrost Control | AY28X079 | AY28X079 | AY28X079 | AY28X079 | |
| Rubber Isolator Kit | BAYISLT101 | BAYISLT101 | BAYISLT101 | BAYISLT101 | |
| Extreme Condition Mount Kit | BAYECMT023 | BAYECMT023 | BAYECMT023 | BAYECMT023 | |
| Start Kit | BAYKSKT263 | BAYKSKT263 | BAYKSKT263 | BAYKSKT263 | |
| Crankcase Heater Kit | BAYCCHT302 | BAYCCHT302 | BAYCCHT302 | BAYCCHT302 | |
| Seacoast Kit | BAYSEAC001 | BAYSEAC001 | BAYSEAC001 | BAYSEAC001 | |
| Low Ambient Kit | BAYLOAM103 | BAYLOAM103 | BAYLOAM103 | BAYLOAM103 | |
| Service Valve Panel Cover | - | - | - | TAYSVPANL0032AA | |
| Refrigerant Lineset (d) | | | | | |

⁽a) Certified in accordance with the Unitary Air-conditioner equipment certification program which is based on AHRI standard 210/240.

⁽b) Calculated in accordance with N.E.C. Only use HACR circuit breakers or fuses.
(c) Standard line lengths – 60', Standard lift – 60' Suction and Liquid line. For Greater lengths and lifts refer to refrigerant piping software Pub#32–3312–0* (* denotes latest revision).

⁽d) 25, 30, 35 and 50 foot linesets available. For a complete listing of lineset options available from equipment or supply stores, refer to the Trane Residential and Light Commercial Product Handbook.



Product Specifications

| Model No. (a) | 4TTR3042N1000A | 4TTR3048N1000A | 4TTR3060N1000A | |
|--------------------------------------|---------------------|---------------------|---------------------|--|
| POWER CONNS. – V/PH/HZ (b) | 208/230/1/60 | 208/230/1/60 | 208/230/1/60 | |
| MIN. BRCH. CIR. AMPACITY | 22 | 24 | 27 | |
| BR. CIR. PROT. RTG MAX. (AMPS) | 35 | 40 | 45 | |
| COMPRESSOR | CLIMATUFF® - SCROLL | CLIMATUFF® - SCROLL | CLIMATUFF® - SCROLL | |
| RL AMPS – LR AMPS | 16.7 - 109 | 18.5 - 124 | 20.8 - 127.1 | |
| Outdoor Fan FL AMPS | 1.05 | 1.05 | 1.05 | |
| Fan HP | 1/5 | 1/5 | 1/5 | |
| Fan Dia (inches) | 23 | 27.5 | 27.5 | |
| Coil | SPINE FIN™ | SPINE FIN™ | SPINE FIN™ | |
| Refrigerant R-410A | 5 LBS., 5 OZ | 5 LBS., 3 OZ | 7 LBS., 10 OZ | |
| VALVE CONNECTION SIZE - IN. O.D. GAS | 7/8 | 7/8 | 7/8 | |
| VALVE CONNECTION SIZE - IN. O.D. LIQ | 3/8 | 3/8 | 3/8 | |
| LINE SIZE – IN. O.D. GAS (c) | 7/8 | 7/8 | 7/8 | |
| LINE SIZE – IN. O.D. LIQ. (c) | 3/8 | 3/8 | 3/8 | |
| Charge Spec. Subcooling | 10°F | 10°F | 10°F | |
| Dimensions H x W X D Crated (IN.) | 34.4 x 35.1 x 38.7 | 34.4 x 35.1 x 38.7 | 42.4 x 35.1 x 38.7 | |
| Weight – Shipping (lbs.) | 216 | 221 | 246 | |
| Weight – Net (lbs.) | 184 | 189 | 211 | |
| Optional Accessories: | | 1 | I | |
| Anti-short Cycle Timer | TAYASCT501A | TAYASCT501A | TAYASCT501A | |
| Evaporator Defrost Control | AY28X079 | AY28X079 | AY28X079 | |
| Rubber Isolator Kit | BAYISLT101 | BAYISLT101 | BAYISLT101 | |
| Extreme Condition Mount Kit | BAYECMT004 | BAYECMT004 | BAYECMT004 | |
| Start Kit | BAYKSKT263 | BAYKSKT263 | BAYKSKT263 | |
| Crankcase Heater Kit | BAYCCHT301 | BAYCCHT301 | BAYCCHT301 | |
| Seacoast Kit | BAYSEAC001 | BAYSEAC001 | BAYSEAC001 | |
| Low Ambient Kit | BAYLOAM103 | BAYLOAM103 | BAYLOAM103 | |
| Service Valve Panel Cover | TAYSVPANL0032AA | TAYSVPANL0044AA | TAYSVPANL0044AA | |
| Refrigerant Lineset (d) | | • | | |

⁽a) Certified in accordance with the Unitary Air-conditioner equipment certification program which is based on AHRI standard 210/240.
(b) Calculated in accordance with N.E.C. Only use HACR circuit breakers or fuses.

⁽c) Standard line lengths – 60', Standard lift – 60' Suction and Liquid line. For Greater lengths and lifts refer to refrigerant piping software Pub#32–3312–0*

 ^{(*} denotes latest revision).
 (d) 25, 30, 35 and 50 foot linesets available. For a complete listing of lineset options available from equipment or supply stores, refer to the Trane Residential and Light Commercial Product Handbook.



Product Specifications

Sound Power Level

| Sound Power Level | | | | | | | | | |
|---|--|-----------------------------|-----------|-----------|-----------|------------|------------|------------|------------|
| MODEL | A-Weighted Sound Power Level [dB(A)] | Full Octave Sound Power(dB) | | | | | | | |
| | | 63 Hz* | 125 Hz | 250 Hz | 500 Hz | 1000 Hz | 2000 Hz | 4000 Hz | 8000 Hz |
| 4TTR3018N | 71 | 74 | 71 | 65 | 68 | 67 | 63 | 56 | 50 |
| 4TTR3024N | 71 | 74 | 71 | 65 | 68 | 67 | 63 | 56 | 50 |
| 4TTR3030N | 71 | 73 | 73 | 72 | 69 | 68 | 60 | 52 | 45 |
| 4TTR3036N | 71 | 73 | 73 | 72 | 69 | 68 | 60 | 52 | 45 |
| 4TTR3042N | 71 | 81 | 72 | 69 | 69 | 66 | 60 | 57 | 54 |
| 4TTR3048N | 71 | 81 | 72 | 69 | 69 | 66 | 60 | 57 | 54 |
| 4TTR3060N | 71 | 81 | 72 | 69 | 69 | 66 | 60 | 57 | 54 |
| Note: Rated in accordance with AHRI Standard 270–2008 *For Reference Only | | | | | | | | | |



Accessory Description and Usage

Anti-Short Cycle Timer — Solid state timing device that prevents compressor recycling until five (5) minutes have elapsed after satisfying call or power interruptions. Use in area with questionable power delivery, commercial applications, long lineset, etc.

Evaporation Defrost Control — SPST Temperature actuated switch that cycles the condenser off as indoor coil reaches freeze-up conditions. Used for low ambient cooling to 30°F with TXV.

Rubber Isolators — Five (5) large rubber donuts to isolate condensing unit from transmitting energy into mounting frame or pad. Use on any application where sound transmission needs to be minimized.

Hard Start Kit — Start capacitor and relay to assist compressor motor startup. Use in areas with marginal power supply, on long linesets, low ambient conditions, etc.

Extreme Condition Mount Kit — Bracket kits to securely mount condensing unit to a frame or pad without removing any panels. Use in areas with high winds, or on commercial roof tops, etc.

AHRI Standard Capacity Rating Conditions

AHRI Standard 210/240 Rating Conditions

- 1. Cooling 80°F DB, 67°F WB air entering indoor coil, 95°F DB air entering outdoor coil.
- High Temperature Heating 47°F DB, 43°F WB air entering outdoor coil, 70°F DB air entering indoor coil
- 3. Low Temperature Heating 17°F DB air entering indoor coil.
- 4. Rated indoor airflow for heating is the same as for cooling.

AHRI Standard 270 Rating Conditions — (Noise rating numbers are determiend with the unit in cooling operations.) Standard Noise Rating number is at 95°F outdoor air.

Model Nomenclature






Figure 1. 018N, 030N, 036N, 042N & 048N Models





Figure 2. 018N, 030N, 036N, 042N & 048N Models



TRANE

Figure 3. 024N Models






Figure 4. 024N Models






Figure 5. 060N Models





LEGEND

FAN CAPACITOR

CF

- WIRE CONNECTOR CN COMPRESSOR CPR CR RUN CAPACITOR STARTING CAPACITOR CS CSR CAPACITOR SWITCHING RELAY ODT OUTDOOR THERMOSTAT HPCO HIGH PRESSURE CUTOUT SWITCH LPCO LOW PRESSURE CUTOUT SWITCH MS COMPRESSOR MOTOR CONTACTOR TNS TRANSFORMER IOL INTERNAL OVERLOAD PROTECTOR COLOR OF WIRE
- COLOR OF MARKER
 BK BLACK RD RED OR ORANGE
 BL BLUE WH WHITE GR GREEN
 BR BROWN YL YELLOW PR PURPLE

BK/BL


FOR CANADIAN INSTALLATIONS
POUR INSTALLATIONS CANADIENNES

CAUTION: NOT SUITABLE FOR USE ON SYSTEMS EXCEEDING 150V-TO-GROUND ATTENTION:NE CONVIENT PAS AUX INSTALLATIONS DE PLUS DE 150 V A LA TERRE

PRINTED FROM DI60439P01 REVA



Figure 6. 060N Models





Mechanical Specification Options

General

The outdoor condensing units are factory charged with the system charge required for the outdoor condensing unit, ten (10) feet of tested connecting line, and the smallest rated indoor evaporative coil match. This unit is designed to operate at outdoor ambient temperatures as high as 115°F. Cooling capacities are matched with a wide selection of air handlers and furnace coils that are AHRI certified. The unit is certified to UL 1995. Exterior is designed for outdoor application.

Casing

Unit casing is constructed of heavy gauge, galvanized steel and painted with a weather-resistant powder paint finish. The corner panels are prepainted. All panels are subjected to our 1,000 hour salt spray test.

Refrigerant Controls

Refrigeration system controls include condenser fan, compressor contactor and low and high pressure switches. A factory supplied, field installed liquid line drier is standard.

Compressor

The compressor features internal over temperature and pressure protection. Other features include: Centrifugal oil pump and low vibration and noise.

Condenser Coil

The outdoor coil provides low airflow resistance and efficient heat transfer. The coil is protected on all four sides by louvered panels.

Low Ambient Cooling

As manufactured, this system has a cooling capacity to 55°F. The addition of an evaporator defrost control permits operation to 40°F. The addition of an evaporator defrost control with TXV permits low ambient cooling to 30°F.

The addition of the BAYLOAM107A low ambient kit permits ambient cooling to 20°F.

Thermostats – Cooling only and heat/cooling (manual and automatic change over). Sub-base to match thermostat and locking thermostat cover.



Trane - by Trane Technologies (NYSE: TT), a global innovator - creates comfortable, energy efficient indoor environments for commercial and residential applications. For more information, please visit trane. com or tranetechnologies.com.





The AHRI Certified mark indicates Trane U.S. Inc. participation in the AHRI Certification program. For verification of individual certified products, go to ahridirectory. org.

Trane has a policy of continuous data improvement and it reserves the right to change design and specifications without notice. We are committed to using environmentally conscious print practices.