

Quick Reference Guide

Precedent™ and Voyager™
Light Commercial
 with eFlex™ Technology



Model Number:

YZ*150-210 YZC036-120
 TZ*150-210 TZC036-120

January 2021

RT-PRC059H-EN

© 2021

1

Table 1. Gas/Electric units

Nominal Tonnage	Model	Cooling Data		Heating Data (Input/output) - (MBh)				Physical Data	
		EER	SEER or IEER	Low	Med	High	Modulating Turn Down = 2.5:1	Dimensions L x W x H (Inches)	Ship Wt. (lbs.)
3	YZC036E3	13.0	20.1	60.0/48.0	80.0/64.0	100.0/80.0	N/A	69 7/8 x 44 1/4 x 36 1/4	658
3	YZC036E4	12.9	19.5	60.0/48.0	80.0/64.0	100.0/80.0	N/A	69 7/8 x 44 1/4 x 36 1/4	690
3	YZC036E3 and Digit 34 = A	13.0	20.1	60.0/48.6	N/A	N/A	N/A	69 7/8 x 44 1/4 x 36 1/4	680
3	YZC036E4 and Digit 34 = A	12.9	19.5	60.0/48.6	N/A	N/A	N/A	69 7/8 x 44 1/4 x 36 1/4	711
4	YZC048F3	13.6	19.4	60.0/49.0	80.0/64.0	120.0/96.0	N/A	88 5/8 x 53 1/4 x 40 7/8	809
4	YZC048F4	13.3	18.5	60.0/49.0	80.0/64.0	120.0/96.0	N/A	88 5/8 x 53 1/4 x 40 7/8	848
4	YZC048F3 and Digit 34 = A	13.6	19.4	60.0/48.6	90.0/72.9	N/A	N/A	88 5/8 x 53 1/4 x 40 7/8	831
4	YZC048F4 and Digit 34 = A	13.3	18.5	60.0/48.6	90.0/72.9	N/A	N/A	88 5/8 x 53 1/4 x 40 7/8	870
5	YZC060E3	12.9	19.6	60.0/49.0	80.0/64.0	130.0/104.0	N/A	88 5/8 x 53 1/4 x 40 7/8	910
5	YZC060E4	12.5	18.4	60.0/49.0	80.0/64.0	130.0/104.0	N/A	88 5/8 x 53 1/4 x 40 7/8	949
5	YZC060E3 and Digit 34 = A	12.9	19.6	60.0/48.6	90.0/72.9	N/A	N/A	88 5/8 x 53 1/4 x 40 7/8	932
5	YZC060E4 and Digit 34 = A	12.5	18.4	60.0/48.6	90.0/72.9	N/A	N/A	88 5/8 x 53 1/4 x 40 7/8	971
6	YZC072F3	12.8	23.2	80.0/64.8	120.0/97.2	150.0/121.5	150.0/121.5	88 5/8 x 53 1/4 x 46 7/8	966
6	YZC072F4	12.6	23.2	80.0/64.8	120.0/97.2	150.0/121.5	150.0/121.5	88 5/8 x 53 1/4 x 46 7/8	966
6	YZC072FW	12.5	22.6	80.0/64.8	120.0/97.2	150.0/121.5	150.0/121.5	88 5/8 x 53 1/4 x 46 7/8	966
7.5	YZC090F3	12.8	22.4	120.0/97.2	150.0/121.5	200.0/162.0	200.0/162.0	88 5/8 x 53 1/4 x 46 7/8	1007
7.5	YZC090F4	12.8	22.4	120.0/97.2	150.0/121.5	200.0/162.0	200.0/162.0	88 5/8 x 53 1/4 x 46 7/8	1007
7.5	YZC090FW	12.8	21.5	120.0/97.2	150.0/121.5	200.0/162.0	200.0/162.0	88 5/8 x 53 1/4 x 46 7/8	1007
8.5	YZC102F3	12.6	22.5	120.0/97.2	150.0/121.5	200.0/162.0	200.0/162.0	88 5/8 x 53 1/4 x 46 7/8	1007
8.5	YZC102F4	12.6	22.5	120.0/97.2	150.0/121.5	200.0/162.0	200.0/162.0	88 5/8 x 53 1/4 x 46 7/8	1007

Table 1. Gas/Electric units (continued)

Nominal Tonnage	Model	Cooling Data		Heating Data (Input/output) - (MBh)				Physical Data	
		EER	SEER or IEER	Low	Med	High	Modulating Turn Down = 2.5:1	Dimensions L x W x H (Inches)	Ship Wt. (lbs.)
8.5	YZC102FW	12.6	21.5	120.0/97.2	150.0/121.5	200.0/162.0	200.0/162.0	88 5/8 x 53 1/4 x 46 7/8	1007
10	YZC120F3	12.1	23.0	150.0/121.5	200.0/162.0	250.0/202.5	250.0/202.5	99 11/16 x 63 3/16 x 50 7/8	1428
10	YZC120F4	12.2	23.0	150.0/121.5	200.0/162.0	250.0/202.5	250.0/202.5	99 11/16 x 63 3/16 x 50 7/8	1428
10	YZC120FW	12.1	22.5	150.0/121.5	200.0/162.0	250.0/202.5	250.0/202.5	99 11/16 x 63 3/16 x 50 7/8	1428
12.5	YZ*150F3	12.5	20.0	150.0/122.0	N/A	250.0/203.0	350.0/283.0	121 11/16 x 84 3/16 x 66 1/4	2680
12.5	YZ*150F4	12.5	20.0	150.0/122.0	N/A	250.0/203.0	350.0/283.0	121 11/16 x 84 3/16 x 66 1/4	2680
15	YZ*180F3	12.7	20.1	250.0/203.0	N/A	350.0/284.0	350.0/283.5	121 11/16 x 84 3/16 x 66 1/4	2686
15	YZ*180F4	12.7	20.1	250.0/203.0	N/A	350.0/284.0	350.0/283.5	121 11/16 x 84 3/16 x 66 1/4	2686
17.5	YZ*210F3	12.3	19.3	250.0/203.0	N/A	350.0/284.0	350.0/283.5	121 11/16 x 84 3/16 x 66 1/4	2766
17.5	YZ*210F4	12.3	19.3	250.0/203.0	N/A	350.0/284.0	350.0/283.5	121 11/16 x 84 3/16 x 66 1/4	2766

* = Downflow or Horizontal

Table 2. Electric/Electric units

Nominal Tonnage	Model	EER	SEER or IEER	kW Range					Dimensions L x W x H (Inches)	Ship Wt. (lbs.)
				6	12	18	N/A	N/A		
3	TZC036E3	13.0	20.1	6	12	18	N/A	N/A	69 7/8 x 44 1/4 x 36 1/4	596
3	TZC036E4	12.9	19.5	6	12	18	N/A	N/A	69 7/8 x 44 1/4 x 36 1/4	628
4	TZC048F3	13.6	19.4	6	12	18	N/A	N/A	88 5/8 x 53 1/4 x 40 7/8	738
4	TZC048F4	13.3	18.5	6	12	18	N/A	N/A	88 5/8 x 53 1/4 x 40 7/8	777
5	TZC060E3	12.9	19.6	6	12	18	23	N/A	88 5/8 x 53 1/4 x 40 7/8	834
5	TZC060E4	12.5	18.4	6	12	18	23	N/A	88 5/8 x 53 1/4 x 40 7/8	873
6	TZC072F3	12.8	23.2	9	18	27	36	N/A	88 5/8 x 53 1/4 x 46 7/8	893
6	TZC072F4	12.6	23.2	9	18	27	36	N/A	88 5/8 x 53 1/4 x 46 7/8	893
6	TZC072FW	12.5	22.6	N/A	18	N/A	36	N/A	88 5/8 x 53 1/4 x 46 7/8	893
7.5	TZC090F3	12.8	22.4	9	18	27	36	N/A	88 5/8 x 53 1/4 x 46 7/8	908
7.5	TZC090F4	12.8	22.4	9	18	27	36	N/A	88 5/8 x 53 1/4 x 46 7/8	908
7.5	TZC090FW	12.8	21.5	N/A	18	N/A	36	N/A	88 5/8 x 53 1/4 x 46 7/8	908
8.5	TZC102F3	12.6	22.5	9	18	27	36	N/A	88 5/8 x 53 1/4 x 46 7/8	908
8.5	TZC102F4	12.6	22.5	9	18	27	36	N/A	88 5/8 x 53 1/4 x 46 7/8	908
8.5	TZC102FW	12.6	21.5	N/A	18	N/A	36	N/A	88 5/8 x 53 1/4 x 46 7/8	908
10	TZC120F3	12.1	23.0	N/A	18	27	36	54	99 11/16 x 63 3/16 x 50 7/8	1302
10	TZC120F4	12.2	23.0	N/A	18	27	36	54	99 11/16 x 63 3/16 x 50 7/8	1302
10	TZC120FW	12.1	22.5	N/A	18	N/A	36	54	99 11/16 x 63 3/16 x 50 7/8	1302
12.5	TZ*150F3	12.5	20.0	18	36	54	N/A	N/A	121 11/16 x 84 3/16 x 66 1/4	2535
12.5	TZ*150F4	12.5	20.0	18	N/A	36	54	N/A	121 11/16 x 84 3/16 x 66 1/4	2535
15	TZ*180F3	12.7	20.1	18	N/A	36	54	N/A	121 11/16 x 84 3/16 x 66 1/4	2541
15	TZ*180F4	12.7	20.1	18	27	36	54	N/A	121 11/16 x 84 3/16 x 66 1/4	2541
17.5	TZ*210F3	12.3	19.3	N/A	N/A	36	54	72	121 11/16 x 84 3/16 x 66 1/4	2616
17.5	TZ*210F4	12.3	19.3	N/A	27	36	54	72	121 11/16 x 84 3/16 x 66 1/4	2616

* = Downflow or Horizontal

Trane and American Standard create comfortable, energy efficient indoor environments for commercial and residential applications. For more information, please visit trane.com or americanstandardair.com.

Trane and American Standard have a policy of continuous product and product data improvement and reserve the right to change design and specifications without notice. We are committed to using environmentally conscious print practices.