

National Line Card | Canada

Products & Systems Solutions



Approach

Our goal is to deliver the outcomes that matter most to you—from more comfortable indoor environments to energy efficient operations. We take a consultative approach to understand your unique business objectives, gather data and information to make informed recommendations, and support you from implementation to validation.

Service & Solutions

Our capabilities include commercial systems, energy services & solutions, contracting, controls/building automation, rentals and service.



Building Services

Help reduce operating costs and extend the life of your equipment with planned, reliable, preventative and proactive scheduled maintenance and repair by Trane factory trained technicians.

- Service Agreements
 - Connected Mechanical Service Agreements
- Extended Warranty
- Quoted Repair Products



Digital Services

Leverage your data and Trane's analytics to create simple dashboards that can help you to understand performance of your building and its assets. Dashboards can help to find opportunities for increasing efficiency, decreasing energy use, and increasing productivity through system optimization.

- Connected Building Service Agreements
- Intelligent Services Agreements
- Secure remote access and building management with TraneConnect™



Intelligent Services

Trane Intelligent Services provides one-on-one consultative support to reduce energy use, manage operational costs, and optimize building performance. Take the guesswork out of understanding building data to achieve more comfortable spaces while meeting your financial and environmental goals.



Energy Services

As a fully accredited Energy Services Provider, Trane enables more efficient, sustainable buildings by providing a single source for decarbonization and modernization solutions, project management services, and financing programs. We use deep expertise and a data driven approach to understand how energy impacts your unique situation, and we partner to develop strategies for energy conservation, resiliency, and optimization.



Rental Services

24/7/365 local service, engineering expertise and an expansive fleet of rental products. Promptly provides temporary, scalable HVAC and power from standard applications to complex solutions

- Water-Cooled Chillers, Air-Cooled Chillers, Temporary Power, Cooling Towers, Packaged A/C Units, Air Handlers, Portable A/C Units



IAQ Services

Today there are more ways than ever to assess and manage indoor air quality, while keeping your goals for cost and sustainability in sight. Trane offers a variety of services, innovative technologies, and proven solutions for measuring and monitoring IAQ. We can help you align with air quality guidelines and recommendations set by the CDC, EPA, and ASHRAE.



Lighting Solutions

Control more than half of your building energy use when you integrate Trane lighting solutions into your BAS.* The Trane difference offers increased energy savings, improved comfort and flexibility, and a higher quality design—all within your budget. Utilizing lighting solutions can enhance productivity, performance, safety, and wellbeing—all while significantly contributing to energy and carbon reduction goals.



Trane Creative Solutions

Customized Trane Equipment Modifications Including: Multizone Replacements, Water-Side Economizer Coils for Air-Cooled Chillers, Packaged Air-Cooled Ice Storage Systems, Acoustical Attenuation



Engineer and Contractor Resources

Trane is here to support, enable and educate Engineers and Contractors through comprehensive tools and resources, design and analysis tools, professional education and training, BIM and CAD drawings, and pre-engineered system solutions. traneengineer.com | tranecontractors.com



Engineered Systems

- Comprehensive Chilled Water Systems
- Comprehensive Chiller- Heater Systems
- CoolSense® Integrated Outdoor Systems
- Intelligent Variable Air Systems
- Thermal Battery™ Systems
- Variable Refrigerant Flow (VRF) Systems
- Zoned Rooftop Systems

Building Automation



Tracer® SC+

Scalable building automation system solution with standard, open protocols



Pivot® Smart Thermostat

Wi-Fi & Ethernet thermostat for light commercial applications



Symbio®

Application Specific and Programmable Unit Controllers, Integrates with BACnet MSTP, BACnet/IP, BACnet/Zigbee, Lontalk & Modbus Protocols



Air-Fi® Zone Sensors

Flexible and reliable wireless sensors & system communications leveraging Air-Fi® Wireless (BACnet/Zigbee) technology. Sensors include temperature, humidity, CO₂ & occupancy

Building Management Systems



Tracer® Ensemble®

Enterprise level building management software for facility professionals



Tracer® Synchrony®

Tracer SC+'s built-in web based user interface software for building operators



Tracer® Concierge®

Light commercial control system with set-up wizard for installers and simple user interface for non-technical users



BAS Operator and Occupant Apps

Providing mobile access to service providers, building operators, and occupants

IAQ Solutions



Synexis

Provides a continuous application of DHP that can reduce airborne and surface pathogens, fungi and VOCs



TCACS

Trane Catalytic Air Cleaning System (TCACS) is an enhanced air filter containing 3 technologies: filtration, germ-killing ultraviolet light, and a photocatalytic oxidation (PCO) process

Trane Precision Cooling



Single Circuit

Single circuit DX or CW; vertical floor mounted; 2 - 10 Ton; tandem compressor options; EC fan technology



Dual Circuit DX

Dual circuit DX or CW; vertical floor mounted; 5 - 80 Tons; EC fan technology



Ceiling Mounted

Ceiling Mounted DX or CW; 1 - 10 Tons; Independently circuited scroll compressors

Water-Cooled Portfolio Centrifugal Chillers



Model TACW

Oil-free; Cooling operation; 60 - 1400 Tons; R-134a and R-513A



Agility® Model HDWA

175 - 425 Tons; Heating and Cooling capable; Up to 140°F HW; 60 Hz, 50 Hz; Symbio® 800 controller; uses either R-513A or R-134A



CentraVac® Model CVHE

3-Stage Compressor; Heating and Cooling capable; Free Cooling; Symbio® 800 controller; 150 - 500 Tons; R-514A



CentraVac® Model CVHF

2-Stage Compressor; Heating and Cooling capable; Free Cooling; Heat recovery operation; Symbio® 800 controller; 325 - 2000 Tons; R-514A



CentraVac® Model CVHH

Multi-stage; Dual Compressor; Heating and Cooling capable; Free Cooling; Heat recovery operation; Symbio® 800 controller; 900 - 2000 Tons; R-1233zd



CentraVac® Model CDHF

Multi-Stage Dual Compressor; Heating and Cooling capable; Free Cooling; Symbio® 800 controller; 1450 - 3950 Tons; R-514A



CentraVac® Model CDHH

Multi-stage; Dual Compressor; Heating and Cooling capable; Free Cooling; Symbio® 800 controller; 1800 - 4000 Tons; R-1233zd

Water-Cooled Chillers



Cold Generator™ Model CGWR

Scroll Compressors; 20 - 75 Tons; R-410A



Series R® Model RTWD

Helical Rotary Compressor; Heating and Cooling capable; Heat recovery operation—dual setpoint; Up to 140°F HW production; 60 - 250 Tons; R-134a or R-513a



Optimus® Model RTHD

Optional Variable Speed Helical Rotary Compressor; Heating and Cooling capable; 150 - 430 Tons; R-134a; or R-513a for fixed speed only

Air-Cooled Chillers



Ascend® Air-to-Water Heat Pump Model ACX

Energy efficient, all electric heating and cooling; Symbio® 800 controller; 140-230 tons cooling; 1500 - 2500 MBh heating; R-454B



Ascend® Model ACS

Scroll Compressor; 140 - 230 Tons; R-454B; Heating and cooling capable; Heat recovery; Symbio® 800 controller



Ascend® Model ACR

Variable Speed Helical Rotary Compressor; Free Cooling; Symbio® 800 controller; 150 - 550 Tons; R-513A



Model CGAM

Scroll Compressor; 20 - 130 Tons; R-454B; Heat recovery option



Model TACA

Oil Free Centrifugal; 60 - 440 Tons; R-134a or R-513A



Sintesis® Model RTAF

Variable Speed Helical Rotary Compressor; 115 - 500 Tons; R-513A; Symbio® 800 controller



Cold Generator™ Model CCAR

Scroll Compressor with Air-Cooled Condenser; 20 - 70 Tons; R-410A

Modular Units



Thermafit™ Model AMC

Air-Cooled Chiller; Free cooling & Heat recovery; 15 - 80 Tons (800 Ton Banks); R-410A



Thermafit™ Model AMT

High efficiency Air-Cooled Chiller; Variable speed compressor and fans; Free cooling & heat recovery; 20 - 40 Tons (400 Ton Banks); High efficiency; R-410A



Thermafit™ Model MWC

Water-Cooled Chiller; Heat recovery; 15 - 80 Tons (800 Ton Banks); R-410A



Thermafit™ Model MWT

High efficiency water-cooled chiller; Variable speed compressor; 20 - 40 Tons (400 Ton Banks); R-410A



Thermafit™ Model AXM

Air-to-water heat pump; Energy efficient; All electric cooling or heating; 30 Ton (300 Ton Banks); R-410A



Thermafit™ Model WXM
Water-to-water heat pump;
Energy efficient; All electric
cooling or heating; 20 - 80 Tons
(800 Ton Banks); R-410A



Thermafit™ Model MWS
Water-cooled multipipe;
Simultaneous heating and
cooling; 30 - 60 Tons (90-480 Ton
Banks); 450 MBh to 7,200 MBh;
R-410A



Thermafit™ Model TACW
Water-cooled chiller; Oil-free
centrifugal; 60 - 135 Tons (1000
Ton Banks); R-134a and R-513A



Cold Generator™ Model CIGD
Water-cooled; Heat Recovery;
20 - 85 Ton (600 ton Arrays)

Thermal Storage



**Thermal Energy
Storage Tanks**
Optimizes energy usage by
storing renewable, excess or
inexpensive energy; Reduces
peak electric demand charges;
Access to demand response
programs; Buildings with chilled
water systems above 100 cooling
tons



**Thermal Battery™
Air-Cooled Chiller Plant**
Pre-Engineered, Factory Built
Cooling System. Incl: Air-Cooled
Chillers, CALMAC® Energy
Storage Tanks, Customizable
System



**Thermal Battery™ Storage-
Source Heat Pump System**
Delivers Heating and Cooling,
Supports Electrification. Incl:
Water-to-Water and Air-to-Water
Heat Pumps, CALMAC® Energy
Storage Tanks, Trane Controls

Packaged Units



Impact®
Cooling, Gas/Electric, Heat Pump
& Dual-Fuel; Multiple Efficiency
Levels; Up to 16 SEER; (1 ph-15
SEER2); 2 - 5 Tons



Foundation®
Cooling, Gas/Electric; Adapts
to Competitors Roof Curbs;
3 - 25 Tons



**Precedent® &
Precedent® with eFlex™**
Cooling, Gas/Electric, Heat Pump
& Hybrid Dual-Fuel; 3-25 Tons,
Multiple Efficiency Levels, eFlex
Variable Speed Compressor; Up
to 26.3 IEER, Symbio 700 and
Mobile App; 6 - 25 Tons



Zoned Rooftop Systems
Pre-designed for small building
comfort; Includes Precedent
or Voyager rooftop unit,
VAV terminal units, Tracer®
Concierge™ system control & Air-
Fi® wireless controls & sensors;
3 - 50 Tons



Voyager® 3
Cooling, Gas/Electric; eStage™
Multi-Stage Compressors; Full &
part load efficiencies; Symbio 700
and Mobile App; Up to 15.8 IEER;
27.5 - 50 Tons



IntelliPak® 1
Cooling, Gas/Electric, Hot
Water; 20 - 130 Tons (Available
with eFlex™ Variable Speed
Compressor; 20 - 75 Tons),
Symbio 800 Controller with 7"
Touchscreen Display, Air-Fi®
Capable



IntelliPak® 2
Cooling, Gas/Electric, Hot
Water, Air-Cooled; 90 - 150 Tons,
Available with eFlex™ Variable
Speed Compressor, Standard
Double Wall Foam, Symbio 800
Controller with 7" Touchscreen
Display, Air-Fi® Capable



IntelliPak® 3
Cooling, Gas/Electric; 20 - 75
Tons, Available with eFlex™
Variable Speed Compressor,
Standard Double Wall Foam,
Symbio 800 Controller with 7"
Touchscreen Display, Air-Fi®
Capable, Up to 17.8 IEER

Self-Contained Units



IntelliPak® Modular Series
Split apart construction, easy
transport & installation; Factory-
installed digital controls; Up to
13.9 EER, 17.9 IEER; Water Cooled
20 - 35 Tons



IntelliPak® Signature Series
Up to 14.1 EER, 19.3 IEER; Floor
by floor system; Factory-installed
digital controls; Water-cooled
20 - 110 Tons



**Modular Self Contained
System**
Smallest Footprint on the Market;
Water-Cooled System; Variable
speed compressors and fans;
Full and part load efficiencies;
Industry-leading Part Load
Efficiency - Up to 20.8 IEER;
40 - 80 Tons, cassette
construction

Water-Source Heat Pumps



**Axiom™ Standard Efficiency
GEH/GEV Models**
Horizontal (0.5 - 15T) or vertical
(0.5 - 25T); Quiet operation;
Multiple airflow configurations;
0.5 - 25 Tons



**Axiom High Efficiency Single-
Stage EXH/EXV Models**
Horizontal or vertical;
Electronically Commuted
Motor (ECM); Rotary or scroll
compressor; 0.75 - 6 Tons



**Axiom High Efficiency
Two-Stage DXH/DXV Models**
Horizontal or vertical; 2-Stage
compressor; Deluxe sound option
for quiet operation; Meets LEED
EAc4 requirement; 2 - 6 Tons



**Axiom Variable Speed
VSH/VSV Models**
Horizontal or vertical; eFlex™
Variable Speed compressors
and fans; Single and three phase
voltage; 2 - 5 Tons



**Axiom High Efficiency
Console GEC Model**
ASHRAE 62 indoor air quality
compliant; Quiet operation;
0.5 - 1.5 Tons



**Axiom Vertical Stack
GET Model**
Multiple capacities & cabinet
sizes; Available in PSC or ECM
motors; Flexible air supply
options; Integrated controls;
0.75 - 3 Tons



**Axiom Water-to-Water
EXW Model**
Co-axial heat exchanger;
Rackable modular design;
5, 10, 20 Tons



**Axiom Rooftop
GWS Model**
Boiler/Tower or Geothermal
applications; Multiple
configuration options;
Microprocessor controls;
3 - 10 Tons

Air Handling Units



**Performance Climate
Changer® - Catalog**
Cost Effective Performance;
Compact Footprint; Factory-
Engineered, Mounted & Tested
Controls; Indoor/Outdoor; Up to
15000 CFM; 2" R-13 Construction



**Performance Climate
Changer® - Semi-custom**
Leading Efficiency and Casing
Performance: Dimensional
Flexibility enabling Easy
Installation: Indoor/Outdoor; Up
to 60000 CFM; up to +/-10 in w.g.;
2", R-13 or 3", R-19 Construction;
Factory Engineered, Mounted &
Tested Controls



Performance Climate Changer – Custom (TCFS/TCPA)

Indoor or Outdoor; Up to 200,000 CFM; Up to +/- 12 inches w.g.; Full dimensional flexibility and thermal performance up to R-25



Trane Air Rotation Unit


Indoor or Outdoor; Up to 300 tons and 120,000+ CFM; CW or DX; 2" Foam Insulated panels, factory engineered & mounted controls

Terminal Units




Blower Coil

Blower Coil Model BCXE; Indoor; Up to 4000 CFM; Horizontal and Vertical Configurations; ECM Motors, Multiple Filter Options, Factory-Engineered & Mounted Controls.



CoolSense® Terminal Unit

Up to 1300 CFM; Variable speed ECM or constant-fan speed; Tracer® UC400 controller (available with Air-Fi wireless)



VariTrane® Model VC*F

Single Duct Variable Air Volume Boxes; 25 - 8000 CFM; Optional Factory Installed Piping Package



VariTrane® Model VDDF

Dual Duct Variable Air Volume Boxes; 80 - 8000 CFM




VariTrane® Model V**F

Fan-Powered Variable Air Volume Boxes; 200 - 3300 CFM; Parallel or Series Configuration



VariTrane® Model L**F

Low Height Fan-Powered Variable Air Volume Boxes; 100 - 1800 CFM; Parallel or Series Configuration



VariTrane® Model VRRF

Round Inlet/Round Outlet RetroFit Variable Air Volume Boxes; 25 - 4000 CFM



UniTrane® Model FC*B

Horizontal or Vertical Fan Coil; Cabinet, Recessed or Compact Configurations; 200 - 1200 CFM



UniTrane® Model FCV

Vertical High Rise Fan Coil Units Vertical stack fan coil; 300 - 1200 CFM



Force-Flo™ Model FF*B

Horizontal or Vertical Cabinet Heater; Concealed or Recessed Configurations; 200 - 1200 CFM



Model VUVE

Vertical Unit Ventilators; 750 - 1500 CFM



Model HUVU

Horizontal Unit Ventilators; 750 - 2000 CFM



Model UHS/UHP

Propeller Unit Heaters; Hydronic & Steam



Model UHWA/UHAA/UHRA/UHXA/UHEC/UHCA

Electric Unit Heaters



Indoor Gas Heating Units

Unit Heaters & Duct Furnaces; High Efficiency >95%

Split Systems



Split Systems

Cooling & Heat Pump; Gas, Electric, or Hot Water Heat; 1.5 - 5 Tons



Odyssey™

Symbio 700 controller ; Full & part load efficiencies; Up to 14.8 IEER; 6 - 25 Tons



RAUJ

Air-Cooled Condensing Units; Available with Remote Chiller Evaporators; 20 - 120 Tons



CAUJ

Air-Cooled Condensers; 20 - 120 Tons

Outdoor Air Solutions



Horizon™ DOAS

DOAS; Packaged product (DX, Air and Water Cooled); Heat Pump, Gas, and Hot Water; <51F Dew Point capability; ERV; AHRI 920 rated



HAXX

Up to 100% outdoor air; Packaged product (DX – Gas Heating); >51F Dew Point capability; ERV; AHRI 340/360 certified; ASHRAE 90.1 compliant

Make-Up Air Gas Heating Units



Model GSAA

Indoor Gas-Fired Make-Up Air Handlers; Standard & High Efficiency; 100 - 1200 MBH



Model GRAA

Outdoor Gas-Fired Make-Up Air Handlers; 100 - 1200 MBH



Model AHOA

Packaged Air Handlers; Cooling, Make-Up Air, & Ventilation

VFD



Trane TR150/TR200 Variable Frequency Drives; 6, 12, 18 Pulse



Trane – by Trane Technologies (NYSE: TT), a global climate innovator – creates comfortable, energy efficient indoor environments through a broad portfolio of heating, ventilating and air conditioning systems and controls, services, parts and supply. For more information, please visit trane.com or tranetechnologies.com.

All trademarks referenced in this document are the trademarks of their respective owners.

© Trane. All Rights Reserved.

EDU-SLB048-EN
01/30/2023