

Trane Light Commercial Replacement Solutions

Complete Portfolio of Heating and Cooling Solutions 25 Tons and Under



Packaged Rooftop Units

GAS/ELECTRIC



Precedent® — YSK/YHK

- 3-5 tons
- R-454B with leak detection (as required)
- Symbio® 700 controls with hinged access panel
- Direct drive fans
- Microchannel condenser and evaporator coils
- Modulating hot gas reheat option
- 2-stage gas heat on all models
- Up to 2 stages of cooling (YSK — 1 stage, YHK — 2 stages)
- Convertible airflow
- Phase monitor
- IAQ sloped drain pan
- Coil guards standard
- Crankcase heater

Precedent® — YSK/YHK

- 6-25 tons
- R-454B with leak detection
- Symbio® 700 controls with hinged access panel
- Direct drive fans
- Microchannel condenser and evaporator coils
- Modulating hot gas reheat option
- 2-stage gas heat or 10:1 modulating gas heat option
- Up to 4 stages of cooling (6-17.5T — 3 stages, 20-25T — 4 stages)
- Convertible airflow
- Phase monitor
- IAQ sloped drain pan removable
- Coil guards standard
- Crankcase heater

LIMITED WARRANTY (Years)

YSK/YHK (3-25 tons)

Compressor — 5
Heat Exchanger — 10 (Aluminized) & 15 (Stainless Steel)
Functional Parts — 3

GDK (3-25 tons)

Compressor — 5
Heat Exchanger — 5 (Aluminized) & 10 (Stainless Steel) - 3-5 tons and 15-25 tons
Functional Parts — 1



Foundation® — GDK

- 3-5 tons
- R-454B with leak detection (as required)
- Electromechanical controls
- Convertible airflow
- Phase monitor
- Fits on commonly found competitor footprint

Foundation® — GDK

- 7.5-25 tons
- R-454B with leak detection
- Electromechanical controls (7.5-12.5 tons)
- Symbio 700 controls (15-25 tons)
- Up to 4 stages of cooling (6-17.5T — 3 stages, 20-25T — 4 stages)
- Convertible airflow
- Phase monitor
- Multispeed motor
- Fits on commonly found competitor footprint

AIR CONDITIONERS



Precedent® — TSK/THK

- 3-5 tons
- R-454B with leak detection (as required)
- Symbio® 700 controls with hinged access panel
- Direct drive fans
- Microchannel condenser and evaporator coils
- Modulating hot gas reheat option
- Up to 2 stages of cooling (TSK — 1 stage, THK — 2 stages)
- Convertible airflow
- Phase monitor
- IAQ sloped drain pan
- Coil guards standard
- Crankcase heater

Precedent® — TSK/THK

- 6-25 tons
- R-454B with leak detection
- Symbio® 700 controls with hinged access panel
- Direct drive fans
- Microchannel condenser and evaporator coils
- Modulating hot gas reheat option
- Up to 4 stages of cooling (6-17.5T — 3 stages, 20-25T — 4 stages)
- Convertible airflow
- Phase monitor
- IAQ sloped drain pan removable
- Coil guards standard
- Crankcase heater

Foundation® — EDK

- 7.5-25 tons
- R-454B with leak detection
- Electromechanical controls (7.5-12.5 tons)
- Symbio 700 controls (15-25 tons)
- Convertible airflow
- Phase monitor
- Multispeed motor
- Fits on commonly found competitor footprint

LIMITED WARRANTY (Years)

TSK & THK (3-25 tons) EDK (3-25 tons)

Compressor — 5 Compressor — 5
Functional Parts — 3 Functional Parts — 1



Foundation® — EDK

- 3-5 tons
- R-454B with leak detection (as required)
- Electromechanical controls
- Convertible airflow
- Phase monitor
- Fits on commonly found competitor footprint

HEAT PUMPS & HYBRID DUAL FUEL



Precedent® — WSK/WHK/DSK/DHK

- 3-25 Tons
- Types: Heat Pumps, Hybrid Dual Fuel
- Efficiency Options: Standard and High
- Controller: Symbio® 700
- Refrigerant: R-454B

LIMITED WARRANTY (Years)

WSK & WHK (3-25 tons)

Compressor — 5
Functional Parts — 3

DSK & DHK (3-25 tons)

Compressor — 5
Heat Exchanger — 10 (Aluminized) & 15 (Stainless Steel)
Functional Parts — 3



Impact™ Rooftop Packaged Unit

- 2-5 Tons
- Types: Cooling Only, Gas/Electric, Heat Pump & Hybrid Dual Fuel
- Efficiency Options: Standard and High
- Controller: Electromechanical
- Refrigerant: R-454B

LIMITED WARRANTY (Years)

Compressor — 5
Heat Exchanger — 5
Functional Parts — 1

Split Systems

AIR CONDITIONERS/ HEAT PUMPS



Odyssey™ — TTA – Cooling

- 6-25 tons
- R-454B with leak detection (as required) & R-410A
- Single, dual or manifolded compressors
- Symbio® 700 controls
- Optional coil guards
- Phase monitor
- Low ambient
- Crankcase heater

Odyssey™ — TWA – Heat Pumps

- 6-25 tons
- R-454B & R-410A
- Single or dual compressors
- Symbio® 700 controls
- Optional coil guards
- Phase monitor
- Crankcase heater

LIMITED WARRANTY (Years)

TTA & TWA

Compressor — 5
Functional Parts — 1

AIR HANDLERS



Odyssey™ — TWE

- 5-25 tons
- R-454B with leak detection (as required) & R-410A
- Dual circuit air handler
- Upflow convertible to horizontal
- Multi-speed standard

LIMITED WARRANTY (Years)

TWE

Functional Parts — 1

Ductless

AIR CONDITIONERS/ HEAT PUMPS



M Series

- Available in 6 different indoor configurations
- Available in single- and multi-zone (up to 8 zones) configurations
- Heat pump condensing units
- Cooling outdoor units only available with wall mounted indoor units
- 9- 6MBH (6MBH wall mounted available in Hyper Heat series only)
- Ideal for light and non-commercial comfort cooling
- 208/230/1/60 (115V available for 9 and 12MBH wall mounted only)
- Indoor unit powered by outdoor unit
- Anti-corrosion treatment applied to condensing unit coil (rated for 2,000 hours salt spray)

P Series

- Available in 6 different indoor configurations
- Cooling only or heat pump outdoor units
- 12-42MBH
- Low ambient cooling available down to -40°F, recommended for critical or 24/7 cooling applications (IT room, etc.)
- Quick restart time
- Long line lengths allowable depending on the system
- 208/230/1/60
- Inverter compressor
- Auto fan mode
- Standard seacoast protection, including 2,000-hour salt spray on condensing unit coil and base panel
- Indoor unit powered by outdoor unit

LIMITED WARRANTY (Years)

Parts:

5 (10 years if registered within 90 days of installation)

Compressor:

7 (10 years if registered within 90 days of installation)

Water Source Heat Pumps



Axiom™ Horizontal & Vertical Water Source Heat Pumps

- Capacity Range: 0.5-25 tons
- Type: Water Source Heat Pumps
- Efficiency Options: Standard, High and Ultra-High Variable Speed
- Unit Controller: Deluxe 24V or Symbio 400-B
- Refrigerant: R-454B

LIMITED WARRANTY (Years)

Compressor: 5
Functional Parts: 1



Axiom™ Vertical Stack Water Source Heat Pumps

- Capacity Range: 0.75-3 tons
- Type: Water Source Heat Pumps
- Efficiency Options: High
- Unit Controller: Deluxe 24V or Symbio 400-B
- Refrigerant: R-454B

LIMITED WARRANTY (Years)

Functional Parts: 1



Contact Your Local Trane Light Commercial Replacement Solutions Team Today

Express@Trane.com



Lisa Kruse

Madison, Milwaukee, Appleton
+1 815-901-6587 Cell
lisa.kruse@trane.com

Hilary Opland

Chicago
+1 773-520-3643
hilary.opland@tranetechnologies.com

Marty Lattanzi

Fargo, Sioux Falls, Twin Cities, La Crosse, Chippewa Falls
+1 262-331-1341 Cell
marty.lattanzi@tranetechnologies.com



All trademarks referenced in this document are the trademarks of their respective owners.

Trane, a brand of Trane Technologies (NYSE: TT), is a global leader in climate solutions for buildings, homes, and industry. Learn more at trane.com or tranetechnologies.com.

© 2026 Trane. All Rights Reserved.