


up to 9 for maximum efficiency and lower energy bills.







# MORE STAGES = MORE COMFORT.

A heat pump's number of stages or speeds determines how efficiently it manages the temperature, humidity, and comfort of your home. Trane's TruComfort™ variable-speed systems can run at 500–750 different speeds to meet heating and cooling demands—delivering the ultimate in whisper-quiet comfort.

# **EFFICIENTLY SIMPLE.**

Trane's two-stage and one-stage systems provide excellent value along with reliable cooling and heating comfort and efficiency. Options include low-profile units, compressor sound insulators and WeatherGuard tops on select models.

Select models include innovative Trane Link technology, which uses Bluetooth to communicate between system components. Simply opt in through the Trane Home app to have your system's data remotely monitored for even the slightest system changes—letting you relax and enjoy the exceptional comfort your variable speed system provides.

XR15 Side Discharge

UPTO 16.0 SEER2

UP TO 8.1 HSPF2



UPTO 16.0 SEER2

XV19 Side Discharge

UPTO 16.2 SFFR2

UPTO 8.1 HSPF2



UPTO 19.0 SEER2 UPTO 9.0 HSPF2

UPTO 16.0 SEER2

UPTO 8.1 HSPF2

Seasonal Energy Efficiency Ratio (SEER2) is an air conditioner's efficiency rating, similar to the miles per gallon for your car.

# WHAT IS HSPF2?

Heating Seasonal Performance Factor (HSPF2) measures heat pump efficiency during the heating season. The higher the number, the more efficient the unit.

\* Trane Link enabled



# SEET® TESTED

Every Trane system is put through some of the most extreme conditions found in nature in our SEET [Systems Extreme Environmental Test] lab. Put through five years of severe wear and tear in just a few months, our products can stand up to the harshest environments imaginable.



AMERICA'S MOST TRUSTED® HVAC BRAND 9 CONSECUTIVE YEARS¹



MOST RELIABLE HEATING AND COOLING EQUIPMENT BRAND $^{\mathrm{2}}$ 

<sup>1</sup>Trane received the highest numerical score in the proprietary Lifestory Research America's Most Trusted® HVAC Brand study for years 2015, 2016, 2017, 2018, 2019, 2020, 2021, 2022 & 2023. Study results are based on experiences and perceptions of people surveyed. Your experiences may vary. Visit www.lifestoryresearch.com

<sup>2</sup>Trane Technologies Marketing Insights. Trane Brand Consumer Survey. June 2021.



WHAT IS SEER2?

# A CLOSER LOOK

#### WeatherGuard™ III Top

Is not only attractive, the durable polycarbonate material provides lasting protection.

Weather Guard III top comes on XV20, XL17 and XL15, and is an optional accessory on select models.

#### **Exclusive Refrigerant-Cooled Inverter**

Helps keep electronics at a consistent temperature, leading to improved performance and reliability.

# Climatuff® Variable Speed Compressor

Is the heart of Trane TruComfort™ technology. It automatically adjusts itself while maintaining constant and consistent comfort.

# **Compressor Sound Insulators**

Reduce operating sound for a quieter home environment.

## Full-Sided Galvanized Steel Louvered Panels

Protect internal components while maintaining airflow efficiency.

### Powder-Paint Finish

Virtually indestructible for maximum protection against corrosion and rust, and years of reliable protection.

\*A Trane UX360 Smart Thermostat and system controller is required for all XV20i, XV18 or XV17 heat pumps.



#### WeatherGuard™ Top (Optional Accessory)

- · Available as an accessory and aftermarket kit
- · Keeps snow, rain, leaves, and debris out
- Reduces icing during severe operating conditions
- · Additional protection for small children playing near unit

# **Integrated Fan System**

Unique blade-down design improves airflow, enhances performance and reduces sound levels.

#### Exclusive All-Aluminum Spine Fin™ Woven Coil

Enhances airflow and heat transfer while resisting corrosion and leaks. They are proven far more reliable than traditional copper and aluminum coils.

#### **Trane Link Communicating Control Board**

Powers the compressor and controls communication between components to optimize your comfort and efficiency.

#### Four Wire Connection

Optional 2 wire connection available.

# DuraTuff™ Rustproof Basepan

Won't crack, corrode, rust or warp.

## WeatherGuard™ Zinc-Coated Fasteners

Provide corrosion resistance and longer life, because even minor details are what Trane reliability is all about.

The XV20i shown is for illustration purposes only. Please note that features and components may vary by model. As part of our continuous product improvement. Trans reserves the right to change specifications and design without notice.

XV20i

FEATURES	XV20i	XV19 Side Discharge	XV18	XV17	XL17	XL15	XR16	XR15 Side Discharge	XR15	XR14
Trane Link Connectivity	Link*	_	Link*	Link Link	_	_	_	-	_	_
ComfortLink™ II Communicating Technology	<b>~</b>	<b>~</b>	<b>~</b>	_	_	_	_	_	_	_
Climatuff® Compressor (stages)	750	500-700**	750	75	2	1	2	1	1	1
Capacity Variability %	25 – 100*	30-100+	25 - 100*	25 – 100*	70/100	100	70/100	100	100	100
Compressor Sound Insulator	<b>~</b>	<b>~</b>	<b>~</b>	~	-	_	-	_	Select Models	-
Overall Sound Power Level [dB(A)]	54 – 76	43-57^	54 – 76	55 - 76	72 – 74	70 – 74	72 – 74	69-74	71 – 75	71 – 76
Spine Fin <sup>™</sup> Coil	~	Plate fin	<b>~</b>	<b>~</b>	<b>~</b>	<b>~</b>	<b>~</b>	Plate fin	<b>~</b>	<b>~</b>
High SEER2 Efficiency (up to)	20.50	19.00	18.00	17.00	17.20	16.00	16.20	16.00	16.00	14.80
High HSPF2 Efficiency (up to)	9.00	9.00	8.50	8.50	8.10	8.10	8.10	8.10	8.10	7.80
WeatherGuard™top	<b>~</b>	_	Optional	Optional	~	<b>~</b>	Optional	_	Optional	Optional
12-year limited warranty compressor, 10-year limited warranty outdoor coil and functional parts with registration.†	~	-	<b>~</b>	~	<b>~</b>	<b>~</b>	_	-	-	-
10 Year limited warranty compressor, outdoor coil and functional parts with registration.†	_	<b>~</b>	_	_	_	_	~	<b>~</b>	~	<b>~</b>

<sup>^</sup> Sound pressure levels per ARI 275

<sup>\*</sup> XV20i, XV18, XV19 vary speed in 1/10 of 1% increments;

XV17 varies speed in 1% increments.
\*\* 2 & 3 ton have 500 stages, 4 ton has 650 stages,

<sup>5</sup> ton has 700 stages + 2 & 3 ton are 50-100%, 4 ton is 35-100%, 5 ton is 30-100%

<sup>†</sup> Registered Limited Warranty terms are available when you register within 60 days of installation. You can register online at Trane.com or by phone at 855-260-2975, otherwise Trane's Base Limited Warranty terms will apply. Base Limited Warranty information on specific products can be found on Trane.com. Ask your dealer for full warranty information at time of purchase. Warranties are for residential and multi-family use only, some exclusions may apply.

Independent install and maintain the right system for of of the pride trained your pertect recommend



#### COMFORT. CONTROL. EFFICIENCY.

Optimize the comfort and efficiency of your home with the Trane Home smart comfort system.

The Trane Home mobile app gives you remote access to your HVAC system through your connected Trane smart thermostat. Adjust your temperature, set your schedule, and view your HVAC usage from anywhere.





Trane Home connects to your Trane HVAC system to provide you with remote control and diagnostics.

To view additional integrations and subscriptions, visit our Knowledge Base at Trane.com/residential/home-subscription/

# WHY IS INDOOR AIR QUALITY IMPORTANT?

We spend 90% of our time indoors, and 70% of that is in our home<sup>2</sup> where the air can be up to 5X poorer quality than the air outside<sup>3</sup>. **To help improve your indoor air, Trane offers a complete** portfolio of air filtration equipment for whole home solutions for new and existing units.



#### TRANE CLEANEFFECTS® AIR CLEANER

Utilizes patented technology to deliver cleaner air to the whole home by removing up to 99.98% of airborne particles<sup>4</sup> that pass through the re-usable filter, including 99.9% of the Influenza A (H1N1) virus<sup>5</sup>. This level of filtration makes it up to 100X more effective than a standard 1" filter<sup>6</sup>. Plus, it's the ONLY whole-home electronic air cleaner that is certified asthma & allergy friendly by the Asthma & Allergy Foundation of America.



Trane CleanEffects® is verified zero ozone producing so you can breathe easier knowing your air is free from harmful byproducts.7



# **ENERGY RECOVERY VENTILATORS (ERV)**

Provide an energy-efficient way to exchange air inside your home with fresh air from outside, removing lingering odors like cooking smells while improving overall air quality.



## **HUMIDIFIERS AND DEHUMIDIFIERS**

Deliver the right amount of moisture to the air throughout your home, adjusting from summer to winter.

Contact your Dealer or visit Trane.com/Residential to learn more.

<sup>4</sup>Based on 3rd party testing of particle removal efficiency down to 0.3 microns (2005) <sup>5</sup>As reported by airmid healthgroup in ASCR092142v2 (2015) | <sup>6</sup>Assuming <1% removal rate of 0.3–10 micron particles <sup>7</sup>Verified Zero Ozone per UL 2998, Intertek certificate #: ZOZ-90113-2022c



It's Hard To Stop A Trane.

All trademarks referenced are the trademarks of their respective owners.

Trane – by Trane Technologies (NYSE: TT), a global climate innovator – creates comfortable, energy efficient indoor environments for commercial and residential applications. For more information, visit Trane.com or TraneTechnologies.com